

[See all 12 Products in Family](#)

TECHSPEC® 50mm Dia. High Performance Glass Linear Polarizer



Stock **#47-217** [CONTACT US](#)

- 1 + MRP ₹26,030

i Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹26,030 each
Qty 6-25	₹20,854 each
Need More?	Request Quote

Product Downloads

General

Linear Polarizer **Type:**

Physical & Mechanical Properties

50.00 **Diameter (mm):**

2.00 ±0.2 **Thickness (mm):**

Parallelism (arcmin):

<4

Dimensional Tolerance (mm):

+0.0/-0.2

Construction:

Dichroic Polarizing Film between Glass

Optical Properties

Coating:

AR: $R_{avg} < 0.5\%$ @ 400 - 700nm

Extinction Ratio:

10,000:1

Substrate: □

Polymer Film between **B270**

Transmission (%):

25 (for random polarization)

Transmission Tolerance (%):

±2

Wavelength Range (nm):

400 - 700

Surface Flatness (P-V):

<1λ (typical)

Polarization Axis Mark (°):

±2

Environmental & Durability Factors

Operating Temperature (°C):

-25 to +65

Regulatory Compliance

RoHS 2015:

Compliant

Reach 224:

Compliant

Certificate of Conformance:

[View](#)

Country of Origin:

Japan

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- 10,000:1 High Extinction Ratio for 400 - 700nm
- Polarization Axis is Reference Marked
- Anti-Reflection Coated to Minimize Reflection Loss

TECHSPEC® High Performance Glass Linear Polarizers offer a high extinction ratio and are available in a range of sizes. A single polarizer transmits about 25% of randomly polarized incident light from 400 – 700nm. The glass substrate is anti-reflection (AR) coated to minimize loss of light due to reflection. TECHSPEC® High Performance Glass Linear Polarizers are ideal for a broad range of industrial and laboratory applications. These glass polarizers are offered in diameters ranging from 6.25mm to 50.80mm.

Technical Information

