


TECHSPEC[®] 50mm Dia. x 125mm FL, SWIR Coated N-BK7 PCX Lens



SWIR Coated N-BK7 Plano-Convex (PCX) Lenses

Stock **#70-277** 2 In Stock

-

1

+

MRP ₹8,374

 Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-9	₹8,374 each
Qty 10-24	₹7,517 each
Qty 25-49	₹6,709 each
Need More?	Request Quote

Product Downloads

General

Plano-Convex Lens

Type:

Physical & Mechanical Properties

50.00 +0.00/-0.025

Diameter (mm):

Bevel:

Protective as needed	
Center Thickness CT (mm):	10.00 ±0.10
Centering (arcmin):	<1
Clear Aperture CA (mm):	45.00
Edge Thickness ET (mm):	4.97

Optical Properties

Effective Focal Length EFL (mm):	
125.00 ±1% and/or 587.6nm	
Substrate: □	N-BK7
f/#:	2.50
Numerical Aperture NA:	0.20
Coating:	BBAR (1650-3000nm)
Wavelength Range (nm):	1650 - 3000
Back Focal Length BFL (mm):	118.47
Coating Specification:	R _{avg} <1% @ 1650 - 3000nm @ 0° AOI R _{abs} <2% @ 1650 - 3000nm @ 0° AOI
Radius R ₁ (mm):	64.60
Surface Quality:	40-20
Power (P-V) @ 632.8nm:	1.5/λ
Irregularity (P-V) @ 632.8nm:	λ/4

Regulatory Compliance

Certificate of Conformance:	
View	
Country of Origin:	United States
Imported By:	Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Low Cost Alternative to Silicon, ZnSe, and Germanium Lenses
- Suitable for Applications in the 1650 – 2500nm Wavelength Range
- Various Coating Options: Uncoated, MgF₂, VIS 0°, VIS-NIR, NIR I, NIR II, VIS-EXT, and YAG-BBAR

TECHSPEC® SWIR Coated N-BK7 Plano-Convex (PCX) Lenses have a positive focal length, making them ideal for collecting and focusing light in imaging applications. Featuring an AR Coating designed to provide less than 0.1% reflection from 1650 – 3000nm, these lenses are ideal for applications utilizing InGaAs sensors with detection ranges up to 2500nm. TECHSPEC® SWIR Coated N-BK7 Plano-Convex (PCX) Lenses are a low cost, lightweight alternative to common infrared lenses manufactured from Silicon, Zinc Selenide, and Germanium substrates. Identical designs of these lenses are also offered uncoated or with broadband anti-reflective (BBAR) coatings, which include MgF₂, VIS 0°, VIS-NIR, NIR I, NIR II, VIS-EXT, and YAG-BBAR. **Note:** While the coating is designed to provide low reflection out to 3000nm, N-BK7’s reduced transmission above 2200nm should be considered when integrating these lenses into sensitive applications.

Coating Curves

