

[See all 31 Products in Family](#)

**TECHSPEC® 50mm Dia. x 200mm FL 785nm V-Coat, UV PCX Lens**



Stock #25-924 **5 In Stock**

MRP ₹33,697

● Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹33,697 each
Qty 6-25	₹26,938 each
Qty 26-49	₹25,324 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Plano-Convex Lens **Type:**

**Physical & Mechanical Properties**

50.00 +0.0/-0.025 **Diameter (mm):**

Protective as needed **Bevel:**

7.00	Center Thickness CT (mm):
<1	Centering (arcmin):
49	Clear Aperture CA (mm):
3.53	Edge Thickness ET (mm):

## Optical Properties

200.00 @ 587.6nm	Effective Focal Length EFL (mm):
Fused Silica	Substrate: <input type="checkbox"/>
4	f#:
0.13	Numerical Aperture NA:
785nm V-Coat	Coating:
195.19	Back Focal Length BFL (mm):
R <sub>abs</sub> <0.25% @ 785nm	Coating Specification:
785	Design Wavelength DWL (nm):
±1	Focal Length Tolerance (%):
91.69	Radius R <sub>1</sub> (mm):
40-20	Surface Quality:
1.5λ	Power (P-V) @ 632.8nm:
M4	Irregularity (P-V) @ 632.8nm:

## Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:
Japan	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

## Product Details

- <0.25% Reflection at 785nm
- 5 - 50mm Diameters Available
- 10 - 250mm EFL Designs Available
- [405nm](#), [532nm](#), [1064nm](#), and [1550nm](#) V-Coated Options Offered

TECHSPEC® Laser Line Coated Fused Silica PCX Lenses are available in a variety of laser line V-Coat AR coating options. Designed for maximum throughput at the specified laser wavelength, these lenses are ideal for applications utilizing low power HeNe, Diode, and Nd:YAG laser sources. With a maximum reflection of <0.25% per surface at the design wavelength, the lenses will provide superior transmission in applications utilizing multiple optical components.