

TECHSPEC® 50mm Dia. x 200mm FL, Uncoated, UV Double-Convex Lens



UV Fused Silica Double-Convex (DCX) Lenses



Stock **#22-429** 10 TO 12 DAYS

[Other Coating Options](#)

- 1 +

₹24,795.00

ADD TO CART

Qty 1-5

₹24,795.00

Qty 6+

₹19,836.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
50.00 +0.0/-0.025

Back Focal Length BFL (mm):

198.39
Effective Focal Length EFL (mm): 200.00
Coating: Uncoated
Coating Specification: Uncoated
Substrate:  Fused Silica (Corning 7980)
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 4.67 ±0.10
Edge Thickness ET (mm): 1.23
Radius R ₁ =R ₂ (mm): 182.65
Clear Aperture CA (mm): 49.00
f/#: 4.00
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.13
Type: Double-Convex Lens
Wavelength Range (nm): 200 - 2200

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View