

TECHSPEC[®] 50mm Dia. x 200mm FL, VIS-NIR, Inked, Achromatic Lens



Stock #49-392-INK 10 TO 12 DAYS
[Other Coating Options](#)

-

1

+

₹17,748.00

ADD TO CART

Qty 1-5
₹17,748.00
Qty 6+
₹14,203.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
50.00 ±0.025

Effective Focal Length EFL (mm):
200.00

Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 194.45
Focal Length Specification Wavelength (nm) : 587.6
Clear Aperture CA (mm) : 49.00
Centering (arcmin) : <1
Center Thickness CT (mm) : 12.50 ±0.20
Center Thickness CT 1 (mm) : 9.00 ±0.10
Center Thickness CT 2 (mm) : 3.50 ±0.10
Radius R₁ (mm) : 130.48
Radius R₂ (mm) : -99.36
Radius R₃ (mm) : -320.20
Edge Thickness ET (mm) : 9.11
Substrate : ☐ N-BAK4 / N-SF10
Surface Quality : 40-20
f/# : 4.00
Numerical Aperture NA : 0.13
Coating : VIS-NIR (400-1000nm)
Coating Specification : R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 400 - 1000

Regulatory Compliance

RoHS 2015 : Compliant
REACH 201 : Compliant
Certificate of Conformance : View