

TECHSPEC<sup>®</sup> 5.0mm Dia. x 5.0mm FL, MgF<sub>2</sub> Coated, Plano-Convex Lens



Stock **#45-228** 20+ In Stock

☐ Other Coating Options

-

1

+

₹3,367

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-9        | ₹3,367 each                   |
| Qty 10-24      | ₹3,017 each                   |
| Qty 25-49      | ₹2,705 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

Type:  
Plano-Convex Lens

Physical & Mechanical Properties

Diameter (mm):  
5.00 +0.0/-0.025

|                      |                           |
|----------------------|---------------------------|
| 30-45, typical       | Centering (arcmin):       |
| 1.87 ±0.05           | Center Thickness CT (mm): |
| 1.00                 | Edge Thickness ET (mm):   |
| 4.5                  | Clear Aperture CA (mm):   |
| Protective as needed | Bevel:                    |

Optical Properties

|                                       |                                  |
|---------------------------------------|----------------------------------|
| 5.00 @ 587.6nm                        | Effective Focal Length EFL (mm): |
| 3.96                                  | Back Focal Length BFL (mm):      |
| MgF <sub>2</sub> (400-700nm)          | Coating:                         |
| R <sub>avg</sub> ≤1.75% @ 400 - 700nm | Coating Specification:           |
| N-LASF44                              | Substrate: □                     |
| 40-20                                 | Surface Quality:                 |
| 1.5λ                                  | Power (P-V) @ 632.8nm:           |
| λ/4                                   | Irregularity (P-V) @ 632.8nm:    |
| ±1                                    | Focal Length Tolerance (%):      |
| 4.02                                  | Radius R <sub>1</sub> (mm):      |
| 1                                     | f/#:                             |
| 0.50                                  | Numerical Aperture NA:           |
| 400 - 700                             | Wavelength Range (nm):           |
| 10 J/cm <sup>2</sup> @ 532nm, 10ns    | Damage Threshold, By Design: □   |

Regulatory Compliance


|           |                             |
|-----------|-----------------------------|
| Compliant | RoHS 2015:                  |
| Compliant | Reach 219:                  |
| View      | Certificate of Conformance: |

## Product Details

- AR Coated to Provide <1.75% Reflectance per Surface for 400 - 700nm
- Designed for 0° Angle of Incidence
- Various PCX Coating Options: [Uncoated](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), [NIR II](#), [VIS-EXT](#), and [YAG-BBAR](#)
- Also Available [Pre-Mounted in Engraved C-Mount Housings](#)


TECHSPEC® MgF2 Coated Plano-Convex (PCX) Lenses have a positive focal length, making them ideal for collecting and focusing light in imaging applications. They are also useful in a variety of applications involving emitters, detectors, lasers, and fiber optics. TECHSPEC® MgF2 Coated Plano-Convex (PCX) Lenses are available in a wide variety of diameters and focal lengths. Identical designs of these PCX lenses are also offered [uncoated](#) or with broadband anti-reflective (BBAR) coatings, which include [VIS 0°](#), [VIS-NIR](#), [NIR I](#), [NIR II](#), [VIS-EXT](#), and [YAG-BBAR](#).

## Technical Information



N-BK7


Uncoated N-BK7 Typical Transmission



Typical transmission of a 3mm thick, uncoated N-BK7 window across the UV - NIR spectra.

[Click Here to Download Data](#)

N-BK7 with MgF<sub>2</sub> Coating Typical Transmission



Typical transmission of a 3mm thick N-BK7 window with MgF<sub>2</sub> (400-700nm) coating at 0° AOI.


The blue shaded region indicates the coating design wavelength range, with the following specification:

$R_{avg} \leq 1.75\% @ 400 - 700\text{nm}$  (N-BK7)

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

N-BK7 with VIS-EXT Coating Typical Transmission



Typical transmission of a 3mm thick N-BK7 window with VIS-EXT (350-700nm) coating at 0° AOI.


The blue shaded region indicates the coating design wavelength range, with the following specification:

$R_{avg} \leq 0.5\% @ 350 - 700\text{nm}$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

N-BK7 with VIS-NIR Coating Typical Transmission







Typical transmission of a 3mm thick N-BK7 window with VIS-NIR (400-1000nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$R_{abs} \leq 0.25\% @ 880\text{nm}$   
 $R_{avg} \leq 1.25\% @ 400 - 870\text{nm}$   
 $R_{avg} \leq 1.25\% @ 890 - 1000\text{nm}$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

|                                                                                                                                                                                                  |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <div>2004006008001000120014001600</div> <div>Wavelength (nm)</div>                                                                                                                               |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |
| <div>N-BK7 with VIS 0° Coating</div> <div>Typical Transmission</div> <div></div> <div>Wavelength (nm)</div>    | <p>Typical transmission of a 3mm thick N-BK7 window with VIS 0° (425-675nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p><math>R_{avg} \leq 0.4\%</math> @ 425 - 675nm</p> <p>Data outside this range is not guaranteed and is for reference only.</p> <p><a href="#">Click Here to Download Data</a></p>                                                                                                          |
| <div>N-BK7 with YAG-BBAR Coating</div> <div>Typical Transmission</div> <div></div> <div>Wavelength (nm)</div> | <p>Typical transmission of a 3mm thick N-BK7 window with YAG-BBAR (500-1100nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p><math>R_{abs} \leq 0.25\%</math> @ 532nm<br/><math>R_{abs} \leq 0.25\%</math> @ 1064nm<br/><math>R_{avg} \leq 1.0\%</math> @ 500 - 1100nm</p> <p>Data outside this range is not guaranteed and is for reference only.</p> <p><a href="#">Click Here to Download Data</a></p>           |
| <div>N-BK7 with NIR I Coating</div> <div>Typical Transmission</div> <div></div> <div>Wavelength (nm)</div>   | <p>Typical transmission of a 3mm thick N-BK7 window with NIR I (600 - 1050nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p><math>R_{avg} \leq 0.5\%</math> @ 600 - 1050nm</p> <p>Data outside this range is not guaranteed and is for reference only.</p> <p><a href="#">Click Here to Download Data</a></p>                                                                                                       |
| <div>N-BK7 with NIR II Coating</div> <div>Typical Transmission</div> <div></div> <div>Wavelength (nm)</div>  | <p>Typical transmission of a 3mm thick N-BK7 window with NIR II (750 - 1550nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p><math>R_{abs} \leq 1.5\%</math> @ 750 - 800nm<br/><math>R_{abs} \leq 1.0\%</math> @ 800 - 1550nm<br/><math>R_{avg} \leq 0.7\%</math> @ 750 - 1550nm</p> <p>Data outside this range is not guaranteed and is for reference only.</p> <p><a href="#">Click Here to Download Data</a></p> |

Coating Curves

# Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

# Compatible Mounts

---