

[See all 33 Products in Family](#)

TECHSPEC® 50mm Dia x 50mm FL, NIR+, High Precision Aspheric Lens



TECHSPEC® High Precision Aspheric Lenses

Stock **#22-909** **1 In Stock**

[Other Coating Options](#)

1 MRP ₹1,10,879

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹1,10,879 each
Qty 6-10	₹99,781 each
Qty 11+	₹93,122 each
Need More?	Request Quote

Product Downloads

General

Aspheric Lens **Type:**

3D Surface Profile not included with coated lenses **Note:**

Physical & Mechanical Properties

50.00 +0.00/-0.025	Diameter (mm):
<1	Centering (arcmin):
45.00	Clear Aperture CA (mm):
4.82	Edge Thickness ET (mm):
13.06	Center Thickness CT (mm):
Protective as needed	Bevel:
Plano	Shape of Back Surface:

Optical Properties

50.00 @587.6nm	Effective Focal Length EFL (mm):
0.50	Numerical Aperture NA:
42.77	Back Focal Length BFL (mm):
N-SF6	Substrate: <input type="checkbox"/>
587.6	Aspheric Design Wavelength (nm):
$\lambda/40$	Asphere Figure Error, RMS @ 632.8nm:
NIR+ (600-1050nm)	Coating:
$R_{avg} < 0.5\%$ @ 600 - 1050nm @ $\pm 30^\circ$ AOI $R_{abs} < 1.5\%$ @ 600 - 1050nm @ $\pm 30^\circ$ AOI	Coating Specification:
40-20	Surface Quality:
1	f#:
600 - 1050	Wavelength Range (nm):
Infinite	Conjugate Distance:
587.6	Focal Length Specification Wavelength (nm):
20.00	Power (diopters):

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 250:
Singapore	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- High Precision Aspheric Surface
- 3D Surface Profiles Included with Uncoated Lenses
- Uncoated and <0.25% Reflectance V-Coat Available

TECHSPEC® High Precision Aspheric Lenses guarantee better than $\lambda/40$ wave aspheric figure error. Achieved via precision magneto-rheological finishing (MRF), these aspheres offer high numerical apertures with diameters ranging from 15 to 50mm and are ideal for a variety of imaging and low light level applications. Each TECHSPEC High Precision Aspheric Lens is individually measured. 3D surface profiles are included with uncoated lenses. For diffraction-limited aspheres designed at specific Nd:YAG laser wavelengths, see our [TECHSPEC High Precision Laser Grade Aspheric Lenses](#).

;