


50mm Diameter, Optical Cast Plastic IR Longpass Filter



Stock **#12-767** 9 In Stock

-

1

+

₹1,635

ADD TO CART

Volume Pricing	
Qty 1-49	₹1,635 each
Qty 50-99	₹1,479 each
Qty 100-249	₹1,323 each
Need More?	Request Quote

Product Downloads

General

Type:Longpass Filter

Physical & Mechanical Properties

50.00	Diameter (mm):
1.97	Diameter (inches):


1.50 Nominal	Thickness (mm):
±0.3	Dimensional Tolerance (mm):
Optical Properties	
Thermoset ADC (CR-39®)	Substrate: □
Uncoated	Coating:
Black	Color:
1.501 @ 20°C	Index of Refraction (n _d):
>90 (typical)	Transmission (%):
57.00	Abbe Number (v _d):
Material Properties	
1.320 at 20°C	Density (g/cm³):
Environmental & Durability Factors	
100 Continuous, 130 One Hour Max	Operating Temperature (°C):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 242:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Lightweight Plastic
- Excellent Thermal and Chemical Resistance

Optical Cast Infrared (IR) Longpass Filters are ideal for blocking visible light while passing near infrared wavelengths. New plastic technology has produced filters with properties that can satisfy a variety of optical and environmental needs at half the weight of glass filters. Compared to similarly available transparent plastics, Thermoset ADC filters have the highest transmission and lowest haze, have at least 25-50 times greater abrasion resistance, and are resistant to all types of chemicals and solvents (acetone, acids, alkali, and alcohols). Optical Cast Infrared (IR) Longpass Filters have excellent thermal characteristics and are resistant to pits from hot sparks resulting from welding or grinding processes. The filters can also be easily drilled with high-speed carbide bits for all mounting types.

Technical Information



Compatible Mounts

;