

TECHSPEC[®] 50mm Dia. x 75mm FL 785nm V-Coat, UV PCX Lens



Stock #25-921 4 In Stock

-

1

+

₹24,056

ADD TO CART

Volume Pricing	
Qty 1-5	₹24,056 each
Qty 6-25	₹19,229 each
Qty 26-49	₹18,061 each
Need More?	Request Quote

Product Downloads

General	
Plano-Convex Lens	Type:
Physical & Mechanical Properties	
50.00 +0.0/-0.025	Diameter (mm):
Protective as needed	Bevel:

12.50	Center Thickness CT (mm):
<1	Centering (arcmin):
49	Clear Aperture CA (mm):
1.72	Edge Thickness ET (mm):

Optical Properties

75.00 @ 587.6nm	Effective Focal Length EFL (mm):
Fused Silica	Substrate: □
1.5	f/#:
0.33	Numerical Aperture NA:
785nm V-Coat	Coating:
66.43	Back Focal Length BFL (mm):
R _{abs} <0.25% @ 785nm	Coating Specification:
785	Design Wavelength DWL (nm):
±1	Focal Length Tolerance (%):
34.39	Radius R ₁ (mm):
40-20	Surface Quality:
1.5λ	Power (P-V) @ 632.8nm:
λ/4	Irregularity (P-V) @ 632.8nm:

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:
Japan	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- <0.25% Reflection at 785nm
- 5 - 50mm Diameters Available
- 10 - 250mm EFL Designs Available
- 405nm, 532nm, 1064nm, and 1550nm V-Coated Options Offered

TECHSPEC® Laser Line Coated Fused Silica PCXLenses are available in a variety of laser line V-Coat AR coating options. Designed for maximum throughput at the specified laser wavelength, these lenses are ideal for applications utilizing low power HeNe, Diode, and Nd:YAG laser sources. With a maximum reflection of <0.25% per surface at the design wavelength, the lenses will provide superior transmission in applications utilizing multiple optical components.