

[See all 6 Products in Family](#)

TECHSPEC® 50mm Diameter 50R/50T, VIS λ /10 Plate Beamsplitter



TECHSPEC® λ /10 Plate Beamsplitters

Stock #34-416 **14 In Stock**

MRP ₹30,974

Price inclusive of all taxes

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-5 | ₹30,974 each |
| Qty 6-49 | ₹24,819 each |
| Need More? | Request Quote |

Product Downloads

General

Standard Beamsplitter **Type:**

Physical & Mechanical Properties

Plate **Construction:**

50.00 **Diameter (mm):**

±0.10 **Dimensional Tolerance (mm):**

Protective Bevel as needed **Edges:**

3.00 ±0.20 **Thickness (mm):**

30 arcmin **Wedge Angle (arcmin):**

Optical Properties

Coating Specification:
Surface 1: 50/50 ±5% @ 550nm, ±10% @ 400 - 700nm
Surface 2: AR $R_{avg} \leq 1\%$, $R_{abs} \leq 2\%$ @ 400 - 700nm

50/50 **Reflection/Transmission Ratio (R/T):**

Fused Silica (Corning 7980) **Substrate:**

M10 **Surface Flatness (P-V):**

20-10 **Surface Quality:**

400 - 700 **Wavelength Range (nm):**

Regulatory Compliance

Compliant **RoHS 2015:**

View **Certificate of Conformance:**

Compliant **Reach 235:**

United States **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91-80-6845 0000

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume


Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- 30 Arcminute Wedge to Minimize Internal Interference
- Wide Range of Splitting Ratios
- Fused Silica Substrate

TECHSPEC® M10 Plate Beam Splitters are designed for use with a 45 degree angle of incidence and random polarization. With a featured 30 arcminute wedge, the effects of internal interference are minimized. Each beamsplitter also includes a multi-layer anti-reflection (AR) coating on the back-surface. TECHSPEC® M10 Plate Beam Splitters have been optimized for the visible spectrum and are offered in a variety of splitting ratios. These beamsplitters are ideal for laser applications due to the wedged design and high quality Fused Silica substrate.

Technical Information



Compatible Mounts
