

TECHSPEC® 5.0mm Diameter x 7.5mm FL, 1550nm V-Coat, PCX Lens



633nm Laser Line Coated Plano-Convex (PCX) Lenses



Stock **#89-048** 10 TO 12 DAYS

[Other Coating Options](#)

- 1 +

₹4,655.00

ADD TO CART

Qty 1-9

₹4,655.00

Qty 10+

₹4,198.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
5.00 +0.0/-0.025

Effective Focal Length EFL (mm):

7.50 @ 587.6nm
Back Focal Length BFL (mm): 6.43
Coating: Laser V-Coat (1550nm)
Coating Specification: R _{abs} <0.25% @ 1550nm
Substrate: ☐ N-SF11
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <3
Center Thickness CT (mm): 1.90 ±0.05
Edge Thickness ET (mm): 1.34
Radius R ₁ (mm): 5.89
Clear Aperture CA (mm): 4.5
f/#: 1.5
Numerical Aperture NA: 0.33
Design Wavelength DWL (nm): 1550
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Damage Threshold, By Design: ☐ 5 J/cm² @ 1550nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant