

## 5.0mm Optic Dia., Optic Mount



Optic Component Mounts

Stock **#64-551** **17 In Stock**

-

1

+

₹2,237

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-9        | ₹2,237 each                   |
| Qty 10+        | ₹2,017 each                   |
| Need More?     | <a href="#">Request Quote</a> |

### Product Downloads

#### General

|          |                 |
|----------|-----------------|
| Fixed    | Type:           |
| Circular | Type of Optics: |

#### Physical & Mechanical Properties

|     |                         |
|-----|-------------------------|
| 4.0 | Clear Aperture CA (mm): |
|     | Outer Diameter (mm):    |

|                         |                                           |
|-------------------------|-------------------------------------------|
| 30.0                    |                                           |
| 12.00                   | Thickness (mm):                           |
| Black Anodized Aluminum | Construction:                             |
| 5.70                    | Max. Thickness of Compatible Optics (mm): |

Threading & Mounting

|                  |                                 |
|------------------|---------------------------------|
| 5.0              | Size of Compatible Optics (mm): |
| M6 x 1.0, 1/4-20 | Compatible Post:                |

Regulatory Compliance

|           |                             |
|-----------|-----------------------------|
| Compliant | RoHS 2015:                  |
| View      | Certificate of Conformance: |
| Compliant | Reach 247:                  |

Product Details

• Simple Mounting Arrangement


• Metric and English Configurations

• Black Anodized Aluminum Construction

• [Posts](#) and [Post Holders](#) Required for Mounting

Optic Component Mounts are designed to hold lenses, filters, mirrors, and other optical components. The included retainer ring securely holds the component in place. Optic Component Mounts need the required [posts](#) and [post holders](#) for mounting to a breadboard. Both English (1/4-20) and Metric (M6) standard posts are accepted by the mounts. These mounts are constructed of black anodized aluminum in a simple mounting arrangement.

Technical Information



| Maximum Optic Diameter | Clear Aperture (CA) | Mount Diameter A | B    | Maximum Optic Thickness T1 | Mount Thickness T2 | Stock No.               |
|------------------------|---------------------|------------------|------|----------------------------|--------------------|-------------------------|
| 5                      | 4                   | 30               | 13.5 | 5.7                        | 12                 | <a href="#">#64-551</a> |
| 6                      | 5                   | 30               | 13.5 | 5.7                        | 12                 | <a href="#">#64-552</a> |
| 9                      | 6                   | 30               | 13.5 | 6                          | 12                 | <a href="#">#64-553</a> |
| 10                     | 7                   | 30               | 13.5 | 6                          | 12                 | <a href="#">#64-554</a> |
| 12                     | 9                   | 35               | 16.0 | 10                         | 16                 | <a href="#">#64-555</a> |
| 12.7                   | 9.5                 | 35               | 16.0 | 10                         | 16                 | <a href="#">#64-556</a> |
| 15                     | 12                  | 35               | 16.0 | 10                         | 16                 | <a href="#">#64-557</a> |
| 18                     | 15                  | 40               | 19.0 | 12                         | 18                 | <a href="#">#64-558</a> |
| 20                     | 17                  | 40               | 19.0 | 12                         | 18                 | <a href="#">#64-559</a> |
| 25                     | 22                  | 45               | 21.5 | 10                         | 16                 | <a href="#">#64-560</a> |
| 25.4                   | 22                  | 45               | 21.5 | 10                         | 16                 | <a href="#">#64-561</a> |
| 25.4                   | 22                  | 45               | 21.5 | 13                         | 19                 | <a href="#">#65-562</a> |
| 30                     | 26                  | 50               | 24.0 | 6                          | 12                 | <a href="#">#64-563</a> |
| 30                     | 26                  | 50               | 24.0 | 12                         | 18                 | <a href="#">#64-564</a> |
| 38.1                   | 34                  | 60               | 29.0 | 12                         | 18                 | <a href="#">#64-565</a> |
| 40                     | 36                  | 60               | 29.0 | 12                         | 18                 | <a href="#">#64-566</a> |
| 50                     | 46                  | 70               | 34.0 | 12                         | 18                 | <a href="#">#64-567</a> |
| 50                     | 46                  | 70               | 34.0 | 18                         | 24                 | <a href="#">#64-568</a> |
| 50.8                   | 46                  | 70               | 34.0 | 12                         | 28                 | <a href="#">#64-569</a> |

