

[See all 102 Products in Family](#)

50mm Diameter x 44mm FL, PCX Condenser Lens



Stock #43-593 **20+ In Stock**

[Other Coating Options](#)

1 MRP ₹4,919

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-10	₹4,919 each
Qty 11-49	₹4,339 each
Need More?	Request Quote

Product Downloads

General

Condenser Lens **Type:**

Physical & Mechanical Properties

50.00 +0.2/-0.4 **Diameter (mm):**

≤25 **Centering (arcmin):**

Center Thickness CT (mm):

18.90 +1.0/-0.4

Bevel:

Protective as needed

Shape of Back Surface:

Plano

Optical Properties

Effective Focal Length EFL (mm):

44.00

Numerical Aperture NA:

0.57

Substrate:

B270

Focal Length Tolerance (%):

±7

Coating:

Uncoated

Surface Quality:

80-50 (typical)

f/#:

0.88

Abbe Number (v_d):

58.3

Index of Refraction (n_d):

1.523

Radius R_2 (mm):

Plano

Wavelength Range (nm):

350 - 2500

Conjugate Distance:

Infinite

Material Properties

Coefficient of Thermal Expansion CTE ($10^{-6}/^{\circ}\text{C}$):

9.4

Regulatory Compliance

Certificate of Conformance:

[View](#)

Country of Origin:

China

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Molded Illumination Lenses
- Aspheric or Spherical Designs
- High Numerical Apertures

Condenser Lenses are molded lenses designed for illumination applications. Featuring large apertures and short focal lengths, Condenser Lenses are commonly used in emitter-detector applications, projection applications, or condensing illumination applications such as Koehler Illumination. The Aspheric Condenser Lenses are molded on the aspheric surface and ground and polished on the opposite face, offering superior performance. The Plano-Convex (PCX) Condenser Lenses are molded on both surfaces, offering excellent value.

Technical Information



