


[See all 26 Products in Family](#)

TECHSPEC® 50mm Square 45°, Magenta Dichroic Filter



Stock #66-253 [CONTACT US](#)

⊖ 1 ⊕ ₹11,210

ADD TO CART

Volume Pricing	
Qty 1-10	₹11,210 each
Qty 11-25	₹10,121 each
Qty 26-49	₹9,576 each
Need More?	Request Quote

Product Downloads

General

Dichroic Filter **Type:**

Physical & Mechanical Properties

50.0 x 50.0 **Dimensions (mm):**

50.00 **Length (mm):**

4.00 ±0.20	Thickness (mm):
50.00	Width (mm):
<1	Parallelism (arcmin):
±0.25	Dimensional Tolerance (mm):
90.00	Clear Aperture (%):

Optical Properties

45.00	Angle of Incidence (°):
495.00	Cut-Off Wavelength (nm):
605.00	Cut-On Wavelength (nm):
N-BK7	Substrate: <input type="checkbox"/>
Traditional Coated	Coating:
Magenta	Color:
R _{abs} = 50% @ 495 & 605nm R _{avg} > 98% @ 400 - 465nm & 635 - 725nm	Reflection (%):
400 - 465 & 635 - 725	Reflection Wavelength (nm):
60-40	Surface Quality:
90.00	Transmission (%):
520 - 580	Transmission Wavelength (nm):
±15	Wavelength Tolerance (nm):
Surface 1: Multi-Layer Dichroic Surface 2: Single Layer MgF ₂	Coating Specification:
400 - 725	Wavelength Range (nm):
λ/4	Surface Flatness (P-V):

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Reflects Stated Color While Transmitting Remaining Visible Spectrum
- Ideal for Color Separation Applications
- Precision N-BK7 Substrates

TECHSPEC® 45° Reflective Dichroic Color Filters are designed to be used at a 45° angle of incidence and will reflect the stated color while transmitting the remaining visible wavelengths. EO's Reflective Dichroics boast higher performance and a better-quality substrate than other readily available color processing filters. Each filter provides greater than 98% reflection over the specified color range and greater than 90% transmission of the remaining wavelengths. TECHSPEC 45° Reflective Dichroic Color Filters are traditionally coated and feature an N-BK7 substrate. These filters are available in circular and square sizes.

Compatible Mounts
