

[See all 7 Products in Family](#)

50mW, 532nm Fiber-Coupled Laser Module



Stock #19-481 **1 In Stock**

- 1 + MRP ₹1,15,758

i Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-9	₹1,15,758 each
Qty 10+	₹1,04,182 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads



General

Diode **Type of Laser:**

Class IIIb **Laser Class - CDRH:**

Physical & Mechanical Properties

Length of Fiber (m):

1

151.00 Length (mm):

Optical Properties

Fiber-Coupled Spatial Mode:

532.00 ±1 Wavelength (nm):

Green Color:

Electrical

50 Output Power (mW):

Hardware & Interface Connectivity

5.0 Operating Voltage (V):

Fiber-Coupled Output Type:

SMA Connector:

Environmental & Durability Factors

+15 to +30 Operating Temperature (°C):

Regulatory Compliance

[Compliant](#) RoHS 2015:

[View](#) Certificate of Conformance:

[Compliant](#) Reach 233:

China Country of Origin:

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- 400µm Core Multimode Fiber with SMA Connector
- 50 and 100mW Output Power Options
- VIS and NIR Wavelengths Available
- [Free Space Alignment Lasers](#) Also Available

Fiber-Coupled Laser Modules feature an integrated 1m long, 400µm core fiber with an SMA905 connector. These cost-effective lasers provide up to 100mW of output power and have a long expected lifetime of 5000 hours. Fiber-Coupled Laser Modules are ideal for use in laser alignment, laser pointing, and laser measurement applications where a free-spaced laser diode module may be difficult to position. These lasers' compact size and easy operation make them well suited for integration into OEM systems.

Note: Power supply is sold separately.