

50mW, 532nm LC Turnkey Laser Fiber SMA



(-) 1 (+) ₹3,10,050

Volume Pricing	
Qty 1-9	₹3,10,050 each
Qty 10+	₹2,79,000 each
Need More?	Request Quote

CAUTION: LASEX IS A LASER
WITH OUTPUT OF 500 MILLIWATT

BEWARE: LASEX
WITH MAX OUTPUT OF 1000 MILLIWATT
CLASS III LASER PRODUCT

<10	Warm-Up Time (minutes):
Diode	Type of Laser:
IIIb	Laser Class - CDRH:

10000	Mean Time to Failure MTTF (hours):
Physical & Mechanical Properties	
142.5 x 60 x 50	Dimensions (mm):
27.4	Beam Height from Base Plate (mm):
Optical Properties	
532.00	Wavelength (nm):
±2	Wavelength Tolerance (nm):
Green	Color:
0.22	Fiber Numerical Aperture NA (1/e²):
Electrical	
50	Output Power (mW):
<2% RMS over 4 hours	Power Stability (%):
1	Modulation Frequency (kHz):
Hardware & Interface Connectivity	
88 x 145 x 83	Power Supply:
90-264VAC	Power Requirement:
Fiber-Coupled	Output Type:
SMA	Connector:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 233:
China	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Multiple Colors and Wavelengths Available
- Ideal for Microscopy Applications
- TE Cooled

Low Cost Turnkey Lasers offer excellent beam quality and output powers up to 50mW. These lasers feature compact designs for simplified integration and manually adjustable output power through the control box. Each laser features TE cooling and flexible interface allowing for digital or analog modulation, with multiple color and wavelength options available. Low Cost Turnkey Lasers are ideal for research, flow cytometry, and microscope illumination applications.

Note: Power supply included. Fiber-coupled lasers include 1m SMA905 coupled fiber.

Technical Information

