

[See all 15 Products in Family](#)

5.0mW 633nm, LDM Focusable Laser Diode



Stock #53-756 **2 In Stock**

- 1 + MRP ₹27,931

i Price inclusive of all taxes

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-9 | ₹27,931 each |
| Qty 10+ | ₹26,535 each |
| Need More? | Request Quote |

Note: This item requires accessories for use | [Learn More](#)

Product Downloads



General

Index Guided Diode, CW **Type:**

Mean Time To Failures MTTF @ 25° (hours):
≥30,000

Drive Circuitry:
Fully shielded, reverse polarity protected

Note:

Includes: Users Manual, Warning Label, and Focus Key

Diode **Type of Laser:**

IIIa **Laser Class - CDRH:**

Physical & Mechanical Properties

22.00 **Weight (g):**

≤20 **Pointing Accuracy (mrad):**

215 **Length of Leads (mm):**

34.00 **Length (mm):**

Optical Properties

635.00 **Wavelength (nm):**

±8 **Wavelength Tolerance (nm):**

0.25 **Wavelength Stability (nm/°C):**

<0.525 **Beam Size at Nearest Focus (µm):**

4 x 2 at Aperture **Beam Diameter (mm):**

<0.5 **Beam Divergence (mrad):**

Red **Color:**

35mm - ∞ **Focus Range (mm):**

Electrical

4.5 (Maximum) **Output Power (mW):**

±5 **Output Power Tolerance (%):**

Hardware & Interface Connectivity

Power Supply:
Power Supply Required and Sold Separately.
USA: [#59-099](#)
Europe: Not Available
Japan: [#59-099](#)
Korea: Not Available
China: [#59-099](#)

3.5 - 5 VDC **Power Requirement:**

red (+), black (-) **Electrical Leads/ Pin Connections:**

Free Space **Output Type:**

Environmental & Durability Factors

-10 to +45 **Operating Temperature (°C):**

-40 to +85 **Storage Temperature (°C):**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 240:**

United Kingdom **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Circular and Elliptical Beam Options
- Bare Leads for Instrument Integration
- Focusable from 20mm to Infinity

Compact LDM Focusable Laser Diode Modules are self-contained and compact and offer a variety of features. They are an ideal replacement for a helium-neon laser in many applications and offer the benefits of superior durability, small size, and a range of wavelengths and powers. Elliptical output beams are produced using a user-adjustable glass focusing lens. Circular output beams are produced using a long focal length plastic lens and are suitable for long-distance and alignment applications. Compact LDM Focusable Laser Diode Modules applications include use as pilot beams for alignment, bar code readers, measurement, dimensional scanning, robotic control, target designation, positioning, and analysis. There is a focusing tool included with all diode modules. Line Generator attachments are available and sold separately for all diode modules listed. [Power Supply](#) is required for operation and is sold separately.

Note: The laser diode case is electrically isolated from the supply voltage.

Technical Information

