

50x50mm Half Mirror Coaxial Light Red

See More by [CCS](#)



Stock #21-835 10 TO 12 DAYS

1 **₹2,31,855**

ADD TO CART

Qty 1+

₹2,31,855

Volume Pricing

[Request Quote](#)

Get Product Downloads

Color:
Red

Input Voltage (V):
24

Model Number:
LFV3-G-50RD

Dimensions (mm):
W 60 mm x D 84 mm x H 57 mm

Wavelength (nm):

630.00

Weight (g):
285

Power Consumption (W):
17

Power Supply:
Power Supply Required and Sold Separately.
USA: [#66-855](#)
Europe: [#66-855](#)
Japan: [#66-855](#)
Korea: [#33-733](#)
China: [#66-855](#)

Active Area (mm):
52 mm x 52 mm

Type of Illumination:
LED Illuminator

Manufacturer:
CCS

Geometry:
Coaxial Light

Illumination Mode:
Constant

Regulatory Compliance

RoHS 2015:
[Exempt](#)

Reach 224:
[Contains SVHC\(s\)](#)

Certificate of Conformance:
[View](#)
