

[See all 6 Products in Family](#)

TECHSPEC® 532nm, 80R/20T, 12.7mm Dia., Nd:YAG Laser Output Coupler



TECHSPEC® Nd:YAG Laser Output Couplers

Stock **#14-742** **20+ In Stock**

⊖ 1 ⊕ MRP ₹14,428

● Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-9	₹14,428 each
Qty 10+	₹12,814 each
Need More?	Request Quote

Product Downloads

General

Laser Output Coupler **Type:**
Arrow on edge points towards S1 **Note:**

Physical & Mechanical Properties

3 **Parallelism (arcmin):**

80	Clear Aperture (%) :
12.70 +0.00/-0.10	Diameter (mm) :
6.35 ±0.20	Thickness (mm) :
Optical Properties	
10-5	Surface Quality :
Coating Specification: S1: R _{avg} = 80±2% @ 532nm @ 0° AOI S2: R _{avg} <0.2% @ 532nm @ 0° AOI	
λ/8	Surface Flatness (P-V) :
Dielectric	Coating Type :
Coating: S1: Partially Reflective Laser Mirror (532nm) S2: Laser V-Coat (532nm)	
80/20	Reflection/Transmission Ratio (R/T) :
532	Design Wavelength DWL (nm) :
0	Angle of Incidence (°) :
Fused Silica (Corning 7980)	Substrate: <input type="checkbox"/>

Regulatory Compliance	
View	Certificate of Conformance :
Lithuania	Country of Origin :
Imported By: Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).


Product Details

- Designs for 532nm and 1064nm Nd:YAG Lasers
- 80% Reflectivity at Nd:YAG DWL
- UV Fused Silica Substrates

TECHSPEC® Nd:YAG Laser Output Couplers are partially reflective mirrors used in laser cavities to transmit a portion of the resonating intracavity beam. The first surface of these output couplers is coated with a partially reflective mirror coating while the back surface is coated with an anti-reflection coating at the laser wavelength to prevent reflection losses. In addition to being used as output couplers, these optics can also be used as partial reflectors for beam attenuation or as general beamsplitters. TECHSPEC Nd:YAG Laser Output Couplers are manufactured from UV fused silica substrates to provide excellent thermal properties and feature laser grade surface specifications. Laser Output Couplers are available with design wavelengths of 532nm or 1064nm for use with Nd:YAG lasers.

Please contact us if your application requires a Laser Output Coupler with a custom design wavelength, size, or reflectivity.

Technical Information



Compatible Mounts
