


TECHSPEC® 514.5nm, 12.5mm Diameter, Raman Edge Filter



Stock **#86-224** **4 In Stock**

- 1 + ₹40,482

ADD TO CART

Volume Pricing	
Qty 1-9	₹40,482 each
Qty 10+	₹33,709 each
Need More?	Request Quote

Product Downloads

General

Longpass Filter **Type:**

Bandwidth (nm): >600 **Note:**

Physical & Mechanical Properties

12.50 +0.0/-0.1 **Diameter (mm):**

±0.1 **Thickness Tolerance (mm):**

Clear Aperture (%):
>80

Optical Properties

Angle of Incidence (°):
0 ±2

Optical Density OD (Average):
≥6.0

Cut-On Wavelength (nm):
519.60

Design Wavelength DWL (nm):
514.5

Substrate:
Fused Silica (Corning 7980)

Coating:
Hard Coated

Rejection Wavelength (nm):
416 - 514.5

Surface Quality:
60-40

Transmission (%):
>93

Transition Width (nm):
<5.1

Transmitted Wavefront, RMS:
<N4 @ 633nm

Coating Specification:
T_{avg} ≥93% @ 521.2 - 1160.5nm

Wavelength Range (nm):
416 - 1161

Laser Blocking Wavelength (nm):
514.5

Threading & Mounting

Mount Thickness (mm):
3.5

Environmental & Durability Factors

Durability:
Environmental: ML-STD-810F
Physical: ML-C-48497A

Regulatory Compliance

RoHS 2015:
Compliant

Certificate of Conformance:
View

Reach 247:
Compliant

Country of Origin:
United States

Imported By:
Edmund Optics India Private Limited

Product Details

- High Transmission for Detecting Weak Signals
- Deep Blocking for Maximum Laser Rejection
- Ideal for Raman Spectroscopy or Life Science Instrumentation

TECHSPEC® Raman Longpass Edge Filters are single filter solutions for reducing spectral noise in Stokes shift applications. These filters are designed to create sharp transitions between transmitted Raman signals and blocked laser wavelengths. Designed to detect even the smallest Raman shifts, TECHSPEC Raman Longpass Edge Filters are ideal for integration into Raman spectroscopy or confocal microscopy systems. The hard coated design offers superior transmission characteristics than comparable traditional coated filters.

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Compatible Mounts
