

[See all 62 Products in Family](#)

Coherent® StingRay™ Line Generator 1231496 | 520nm, 35mW, 30° Fan Angle

See More by [Coherent®](#)



Stock #86-854 2 In Stock

-

1

+

₹1,24,200

ADD TO CART

Volume Pricing	
Qty 1+	₹1,24,200 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads



General	
Coherent®	Manufacturer:
Diode	Type of Laser:
IIIb	Laser Class - CDRH:

1231496	Model Number:
Physical & Mechanical Properties	
<10	Pointing Stability (μrad/°C):
97.80	Length (mm):
Optical Properties	
TEM ₀₀	Spatial Mode:
520.00	Wavelength (nm):
<1.5	Mode Quality, M ² :
±10	Wavelength Tolerance (nm):
Green	Color:
30.00	Fan Angle (°):
Electrical	
35	Output Power (mW):
Max Analog: 500	Modulation Frequency (kHz):
Hardware & Interface Connectivity	
Power Supply: Power Supply Required and Sold Separately. USA: #86-878 Europe: #86-878 Japan: #86-878 Korea: #86-878 China: #86-878	
Electrical Leads/ Pin Connections: Hirose HR-10P-12S	
Free Space	Output Type:
5 - 24 DC	Input Voltage (V):
Environmental & Durability Factors	
10 to 40	Operating Temperature (°C):
-20 to +60	Storage Temperature (°C):
Regulatory Compliance	
Exempt	RoHS 2015:
Contains SVHC(s)	Reach 224:
View	Certificate of Conformance:
Singapore	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

For CDRH certified systems, class IIIb lasers require [#86-878](#). These lasers include a Hirose connector and flying lead terminals for compatibility with a variety of power supplies.

- External Focus with up to 100mW Output Power
- Auto Scaling Input Power 5 - 24VDC with Reverse Polarity Protection
- Built-In Microcontroller for Fault Monitor
- [Coherent® StingRay™ Developer's Kit](#) also available

Coherent® StingRay™ and BioRay™ Laser Diode Modules are ideal for a variety of alignment, machine vision, and biomedical applications. They are available in a wide range of output powers, wavelengths, and fan angles. High precision optical components and sophisticated drive electronics provide power and control to your application, reducing signal-to-noise ratios and increasing measurement speed. Coherent® StingRay™ and BioRay™ Laser Diode Modules are designed with a flat top power distribution across the beam profile for consistency in line projection widths.

Note: For CDRH certified systems (Class IIIb), [#86-878](#) Laser Controller and additional external voltage source (0.5-5V) with BNC connector is required.