

[See all 36 Products in Family](#)

TECHSPEC®

535nm CWL, 25mm Dia, 43nm Bandwidth, Unmounted OD 6 Fluorescence Bandpass Filter



Stock **#18-392** **20+ In Stock**

[Additional Bandwidths](#)

- 1 + MRP ₹34,303

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹34,303 each
Qty 6-25	₹27,442 each
Qty 26-49	₹25,728 each
Need More?	Request Quote

Product Downloads

General

Bandpass Filter **Type:**

Cy3 Excitation / FITC Emission **Compatible Fluorophore:**

Physical & Mechanical Properties

25.00 ±0.1 **Diameter (mm):**

22.50 **Clear Aperture CA (mm):**

2.00 ±0.1 **Thickness (mm):**

Unmounted **Construction:**

Physical Durability:
Adhesion per ML-PRF-13830B, Section C.4.5.12
Moderate abrasion per ML-PRF-13830B, Section C.4.5.11
Cleaning per ML-C-48497A Section 4.5.4.2

Protective as needed **Bevel:**

Optical Properties

0 ±5 **Angle of Incidence (°):**

43.00 **Bandwidth (nm):**

250 - 497 & 588 - 1000 **OD 6 Blocking Wavelength Range (nm):**

≥6.0 **Optical Density OD (Average):**

>93 over Bandwidth **Average Transmission (%):**

534.50 **Center Wavelength CWL (nm):**

48.00 **Full Width-Half Max FWHM (nm):**

Substrate:
[Fused Silica](#) (Corning 7980)

93 **Minimum Transmission (%):**

Hard Coated **Coating:**

60-40 **Surface Quality:**

250 - 1100 **Blocking Wavelength Range (nm):**

λ/4 (prior to coating) **Transmitted Wavefront, RMS:**

Environmental & Durability Factors

Environmental Durability:
Humidity per ML-STD-810H, Section 507.6
Temperature per ML-STD-810H, Section 501.7 and 502.7

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 247:**

United States **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Designed for Use With Common Fluorophores
- Excitation and Emission Filters Available
- High Transmission with Deep >OD 6.0 Blocking
- Mounted [Fluorescence Filters](#) and [Mounted Fluorescence Filter Sets](#) Also Available

TECHSPEC® Unmounted Fluorescence Bandpass Filters are designed with center wavelengths and bandwidths that match the excitation and emission wavelengths of common fluorophores. These filters feature high transmission up to >93% in their passband with deep >OD 6.0 blocking outside of their passband, resulting in high contrast images when used in fluorescence imaging systems. The low transmitted wavefront error of these filters further enhances image quality by minimizing image distortion. TECHSPEC Unmounted Fluorescence Bandpass Filters are available with a 12.5 or 25mm diameter and are ideal for integration into life science and biotech instrumentation including polymerase chain reaction (PCR) testing platforms, DNA sequencers, fluorescence detectors, flow cytometers, and fluorescence imaging systems.
