

[See all 3 Products in Family](#)

**TECHSPEC® 532, 1064nm, 50.8mm, Dual-Band AR Fused Silica Window**



Stock #17-589 **16 In Stock**

MRP ₹28,047

**i** Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹28,047 each
Qty 6-25	₹22,499 each
Qty 26-49	₹21,087 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Laser Line Window Type:  
 Glass Type of Window:

**Physical & Mechanical Properties**

45.72 Clear Aperture CA (mm):

50.80 +0.00/-0.10	<b>Diameter (mm):</b>
6.35 ±0.20	<b>Thickness (mm):</b>
<3	<b>Parallelism (arcmin):</b>
Fine Ground	<b>Edges:</b>

## Optical Properties

0	<b>Angle of Incidence (°):</b>
Dual-Band (532, 1064nm)	<b>Coating:</b>
532, 1064	<b>Design Wavelength DWL (nm):</b>
Fused Silica (Corning 7980)	<b>Substrate:</b> <input type="checkbox"/>
10-5	<b>Surface Quality:</b>
R <sub>abs</sub> <0.25% @ 532nm, R <sub>abs</sub> <0.10% @ 1064nm	<b>Coating Specification:</b>
λ/10	<b>Surface Flatness (P-V):</b>
5J/cm <sup>2</sup> @ 532nm, 20ns, 20Hz; 15J/cm <sup>2</sup> @ 1064nm, 20ns, 20Hz	<b>Damage Threshold, By Design:</b> <input type="checkbox"/>

## Material Properties

7980 0F	<b>Fused Silica Grade:</b>
---------	----------------------------

## Regulatory Compliance

<a href="#">View</a>	<b>Certificate of Conformance:</b>
United States	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91-80-6845 0000	<b>Imported By:</b>

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- 532 and 1064nm Dual-Band Anti-Reflection Coating
- 10-5 Surface Quality and λ/10 Surface Flatness
- Ideal for Nd:YAG Laser Systems
- [Uncoated Laser Window Substrates](#) Available

TECHSPEC® Dual-Band Anti-Reflection (AR) Laser Windows provide high performance AR coatings designed to be used in multi-wavelength laser applications. The anti-reflection coatings on both surfaces feature <0.25% reflection at 532nm and <0.1% reflection at 1064nm, significantly increasing laser throughput. These laser windows feature excellent thermal stability, precision grade λ/10 surface flatness, and 10-5 surface quality, ensuring minimal distortion to transmitted beams. TECHSPEC® Dual-Band Anti-Reflection (AR) Laser Windows are available in standard imperial sizes for convenient integration into existing laser systems and are ideal for Nd:YAG applications including those used in aesthetic laser systems. [Contact us](#) if your application requires a custom coating or design.

**Note:** Damage thresholds values are tested independently.

## Technical Information

532 & 1064nm Dual-Band AR Coated Laser Window

