

[See all 12 Products in Family](#)

532nm, 1X - 4X Jenoptik Variable Beam Expander

See More by [Jenoptik](#)



Stock #73-089 [CONTACT US](#)

MRP ₹92,773

Price inclusive of all taxes

[ADD TO CART](#)

Volume Pricing	
Qty 1-4	₹92,773 each
Qty 5+	₹83,687 each
Need More?	Request Quote

Product Downloads

General

Beam Expander **Type:**
Variable Magnification **Style:**

Physical & Mechanical Properties

127.90 **Length (mm):**

190	Weight (g):
37.6	Housing Diameter (mm):
Optical Properties	
4.0 (1X- 4X)	Entrance Aperture (mm):
1X- 4X	Expansion Power:
Entrance: Fused Silica Exit: Fused Silica	Substrate: <input type="checkbox"/>
≥97	Transmission (%):
532	Design Wavelength DWL (nm):
515 - 540	Wavelength Range (nm):
CW: 0.50 MW/cm ² Pulsed (ns): 0.50 J/cm ²	Damage Threshold, Reference: <input type="checkbox"/>
547	GDD Specification (fs²):

Threading & Mounting	
Input M30 X 1.0	Mounting Threads:

Regulatory Compliance	
View	Certificate of Conformance:
Lithuania	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details

- Ideal for High-Power and Ultrashort Pulse Systems
- Continuous Magnifications Ranges from 1X to 10X
- Designed for Diffraction Limited Performance

Jenoptik Variable Magnification Beam Expanders provide excellent performance with high damage thresholds for the demanding requirements of laser materials processing. These beam expanders are coated to maximize transmission at common Nd:YAG and Fiber Laser Wavelengths, and are available in a variety of design forms and zoom ranges. The standard variable magnification beam expanders are available in a 1X to 4X or 2X to 10X configuration and features all fused silica optics, and designs for either 355nm, 515-540nm, or 1030-1080nm. The 1X to 4X steadfast versions are available in the same wavelength ranges and feature a mechanical design that guides the movable optical elements in a stable, linear manner to reduce the influences of vibrations or system accelerations. The Silverline™ series are designed for high performance and ensure diffraction-limited image quality over the entire 1X to 8X magnification range. Jenoptik Variable Magnification Beam Expanders are ideal for a range of high-power laser material processing applications including cutting, welding, and engraving for metals, polymers, or ceramics.