

[See all 13 Products in Family](#)

## 532nm, $\lambda/4$ Polymer Waveplate



Polymer Waveplates (Retarders)

Stock #90-939 **8 In Stock**

1  MRP ₹33,495

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹33,495 each
Qty 6-25	₹26,837 each
Qty 26+	₹24,415 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Polymer Waveplate **Type:**

#### Physical & Mechanical Properties

25.00 **Diameter (mm):**

**Thickness (mm):**

2.00 ±0.2

Parallelism (arcmin):

3.00

Dimensional Tolerance (mm):

+0.0/-0.2

Construction:

Birefringent Polymer Stack

## Optical Properties

Coating:

R<sub>avg</sub> <0.5% @400 - 700nm

Design Wavelength DWL (nm):

532

Substrate: □

B270

Retardance:

λ/4

Retardance Tolerance (nm):

±10 @532

Retardance Order:

0

## Regulatory Compliance

RoHS 2015:

Compliant

Reach 224:

Compliant

Certificate of Conformance:

[View](#)

Country of Origin:

Japan

Imported By:

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- True Zero Order Waveplate Performance
- λ/4 and λ/2 Retardance
- Available with Multiple Wavelengths or Achromatic Designs

Polymer Waveplates (Retarders) are durable, low-cost alternatives to quartz waveplates that feature a thin birefringent polymer film layered between two glass windows. The waveplates are designed to act as true zero order waveplates, providing stable performance over wavelength shift and wide angles of incidence. Due to their cemented construction and plastic birefringence material, these waveplates, or retarders, are not recommended for high power laser use or for extreme temperature shifts. Polymer Waveplates (Retarders) have either λ/4 and λ/2 retardance. They are offered in 405 to 650nm.

**Note:** Fast axis is marked on the edge of the glass.

;