

[See all 159 Products in Family](#)

TECHSPEC<sup>®</sup> 575nm CWL, 25mm Dia. Hard Coated OD 4.0 50nm Bandpass Filter



Stock #86-952 10 In Stock

[Additional Bandwidths](#)

-

1

+

₹20,163

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | ₹20,163 each                  |
| Qty 6-25       | ₹15,881 each                  |
| Qty 26-49      | ₹14,792 each                  |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| General           |                       |
|-------------------|-----------------------|
| Bandpass Filter   | Type:                 |
| Bo-Pro 3, KFP-Red | Typical Applications: |

| Physical & Mechanical Properties |                |
|----------------------------------|----------------|
| 25.00 +0.0/-0.1                  | Diameter (mm): |

|                                                                                                                                                   |                         |
|---------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------|
| 21.0                                                                                                                                              | Clear Aperture CA (mm): |
|                                                                                                                                                   |                         |
| Mounted in Black Anodized Ring                                                                                                                    | Construction:           |
|                                                                                                                                                   |                         |
| Adhesion per ML-PRF-13830B, Section C.4.5.12<br>Moderate abrasion per ML-PRF-13830B, Section C.4.5.11<br>Cleaning per ML-C-48497A Section 4.5.4.2 | Physical Durability:    |

|          |                           |
|----------|---------------------------|
| 3.5 ±0.5 | Substrate Thickness (mm): |
|----------|---------------------------|

Optical Properties

|               |                                     |
|---------------|-------------------------------------|
| 0             | Angle of Incidence (°):             |
|               |                                     |
| 45            | Bandwidth (nm):                     |
|               |                                     |
| ≥4.0          | Optical Density OD (Average):       |
|               |                                     |
| 575.00        | Center Wavelength CWL (nm):         |
|               |                                     |
| 50.00         | Full Width-Half Max FWHM (nm):      |
|               |                                     |
| Optical Glass | Substrate: <input type="checkbox"/> |
|               |                                     |
| ≥90           | Minimum Transmission (%):           |
|               |                                     |
| Hard Coated   | Coating:                            |
|               |                                     |
| 80-50         | Surface Quality:                    |
|               |                                     |
| 200 - 1200    | Blocking Wavelength Range (nm):     |

Threading & Mounting

|          |                       |
|----------|-----------------------|
| 5.0 ±0.1 | Mount Thickness (mm): |
|----------|-----------------------|

Environmental & Durability Factors

|                                                                                                 |                           |
|-------------------------------------------------------------------------------------------------|---------------------------|
| Humidity per ML-STD-810H, Section 507.6<br>Temperature per ML-STD-810H, Section 501.7 and 502.7 | Environmental Durability: |
|-------------------------------------------------------------------------------------------------|---------------------------|

Regulatory Compliance

|                                     |                             |
|-------------------------------------|-----------------------------|
| Compliant                           | RoHS 2015:                  |
|                                     |                             |
| View                                | Certificate of Conformance: |
|                                     |                             |
| Compliant                           | Reach 247:                  |
|                                     |                             |
| United States                       | Country of Origin:          |
|                                     |                             |
| Edmund Optics India Private Limited | Imported By:                |


## Product Details

- High Transmission, Deep Blocking
- Broad Bandwidths Ideal for Imaging Applications
- Available in VIS and IR Center Wavelengths
- Hard Coated OD 4.0 10nm and 25nm Bandpass Filters Also Available

TECHSPEC® Hard Coated OD 4.0 50nm Bandpass Filters are ideal for imaging applications , including machine vision inspection, fluorescence microscopy, and a variety of biotech instrumentation. These bandpass filters eliminate unwanted background noise and enhance the signal-to-noise ratio within imaging applications. Unlike traditional filters , these hard coated filters are fabricated using only a single substrate. TECHSPEC® Hard Coated OD 4.0 50nm Bandpass Filters offer deeper blocking, higher transmission, and steeper slopes than traditional coated filters. Hard Coated OD 4.0 10nm and 25nm are also available.

**Note:** These filters are optimized for high spectral performance rather than high Laser Induced Damage Thresholds (LIDT). A typical LIDT for these filters is 1 J/cm<sup>2</sup> @ 532nm, 10ns. Please [contact us](#) if you require a filter with a higher LIDT value.

## Technical Information



*All mounted TECHSPEC® Optical Filters have an arrow on the side of the mount that points to the filter-coated surface for quick reference. Filter oriented such that arrow points to filter coated surface S1. Anti-reflective (AR) coating is applied to S2.*

## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Compatible Mounts

---