

[See all 55 Products in Family](#)

37mm Max. Aperture, Mounted Iris Diaphragm



Stock #23-252 **1 In Stock**

- 1 + MRP ₹8,829

i Price inclusive of all taxes

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-4 | ₹8,829 each |
| Qty 5-9 | ₹7,781 each |
| Qty 10-25 | ₹7,166 each |
| Need More? | Request Quote |

Product Downloads

General

Mounted **Type:**

Physical & Mechanical Properties

37.0 **Maximum Aperture (mm):**

78.0 **Outer Diameter (mm):**

Construction:
Brass Housing, Blue Tempered Steel Leaves

Inner Diameter (mm):
53.0

Lever Diameter (mm):
3.00

Lever Length (mm):
12.50

Number of Leaves:
16.00

Thickness (mm):
6.00

Optical Properties

Minimum Aperture (mm):
1.9

Threading & Mounting

Mounting Threads:
8-32

Set Screw Thread:
4-40

Regulatory Compliance

RoHS 2015:
[Exempt](#)

Certificate of Conformance:
[View](#)

Reach 235:
[Contains SVHC\(s\)](#)

Country of Origin:
Germany

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Used to Adjust $f\#$, Field Stop Diameter, and Overall Light Throughput
- Mounted Version Features a Tapped Hole for Post Mounting
- Abundant Types for Varying Applications


Standard Series Iris Diaphragms can provide control of system $f\#$ ($f\# = \text{focal length}/\text{effective diameter}$), field stop diameter, and overall energy throughput when incorporated into standard optical systems. It should be noted that the location of the iris is critical to how it will affect the system. All of these diaphragms offer exceptionally smooth operation over the lever travel, from maximum to minimum aperture (approximately 90°). Mounted versions of these diaphragms feature a tapped hole for easy post mounting. Standard Series Iris Diaphragms have blued spring steel leaf construction and black housing finish with lever actuators that are available in two styles: stainless steel "pin" or plastic "tab." These diaphragms are specifically designed for OEM integration and general laboratory use.

For specific OEM application assistance, please contact our [Applications Engineering Department](#).

Note: [Iris Diaphragm Mounts](#) sold separately.

Technical Information

Types of Levers



| Outside Diameter A | Maximum Aperture B | Minimum Aperture C | Thickness D | Stock No. |
|--------------------|--------------------|--------------------|-------------|-------------------------|
| 10.0 | 5.0 | 0.60 | 4.50 | #54-352 |
| 14.8 | 8.00 | 0.80 | 4.50 | #32-623 |
| 15.5 | 8.50 | 1.00 | 5.30 | #42-124 |

| | | | | |
|-------|-------|------|------|---------|
| 19.8 | 12.0 | 0.80 | 5.0 | #30-263 |
| 22.0 | 14.0 | 1.0 | 6.0 | #42-123 |
| 24.0 | 15.0 | 1.2 | 5.0 | #32-622 |
| 28.0 | 18.0 | 1.2 | 5.0 | #32-621 |
| 30.0 | 20.0 | 1.2 | 5.5 | #35-111 |
| 31.0 | 18.0 | 1.5 | 6.5 | #36-623 |
| 33.0 | 22.0 | 1.4 | 5.5 | #32-620 |
| 37.0 | 25.0 | 0.8 | 5.5 | #35-110 |
| 40.0 | 28.0 | 1.5 | 5.5 | #42-122 |
| 42.0 | 42.6 | 1.2 | 5.8 | #40-997 |
| 42.0 | 30.0 | 1.5 | 6.0 | #64-500 |
| 48.0 | 48.0 | 1.2 | 6.8 | #40-998 |
| 48.5 | 30.0 | 1.2 | 7.0 | #42-121 |
| 49.0 | 34.0 | 1.5 | 6.5 | #41-972 |
| 50.0 | 36.0 | 1.9 | 6.0 | #32-619 |
| 53.0 | 37.0 | 1.9 | 6.0 | #32-618 |
| 55.0 | 41.0 | 2.0 | 6.5 | #41-973 |
| 58.0 | 42.0 | 2.0 | 6.5 | #30-118 |
| 60.0 | 40.0 | 2.5 | 7.8 | #36-624 |
| 70.0 | 50.0 | 2.5 | 7.5 | #32-617 |
| 77.0 | 59.0 | 7.0 | 8.0 | #32-616 |
| 80.0 | 58.0 | 3.0 | 8.0 | #32-615 |
| 82.0 | 60.0 | 4.0 | 10.1 | #36-625 |
| 92.0 | 70.0 | 4.5 | 9.0 | #32-614 |
| 100.0 | 75.0 | 4.5 | 9.0 | #30-264 |
| 110.0 | 80.5 | 4.5 | 10.0 | #32-613 |
| 120.0 | 90.0 | 5.0 | 12.0 | #32-612 |
| 130.0 | 98.0 | 5.0 | 12.0 | #32-611 |
| 140.0 | 104.0 | 5.0 | 11.0 | #32-610 |
| 150.0 | 110.0 | 6.0 | 13.0 | #60-644 |
| 165.0 | 120.0 | 6.0 | 15.0 | #32-609 |
| 180.0 | 138.0 | 11.5 | 13.0 | #32-608 |
| 208.0 | 158.0 | 11.0 | 16.0 | #70-894 |
| 300.0 | 225.0 | 12.0 | 19.0 | #70-895 |

