

TECHSPEC®

540nm CWL, 50mm Dia, 50nm Bandwidth, OD 6 Fluorescence Filter



Stock #86-366

10 TO 12 DAYS

[Additional Bandwidths](#)



1



₹73,776.00

ADD TO CART

Qty 1-5
₹73,776.00
Qty 6+
₹60,639.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):

50.00 +0.00/-0.10

Angle of Incidence (°):

0 ±5

Bandwidth (nm):

50.00

OD 6 Blocking Wavelength Range (nm): 450 - 500
Optical Density OD (Average): ≥6.0
Clear Aperture CA (mm): 45.21
Center Wavelength CWL (nm): 540.00
Full Width-Half Max FWHM (nm): 56.00
Substrate:  Fused Silica (Corning 7980)
Minimum Transmission (%): >93
Coating: Hard Coated
Surface Quality: 60-40
Thickness Tolerance (mm): ±0.1
Transmission (%): >93
Type: Bandpass Filter
Blocking Wavelength Range (nm): 250 - 1100
Construction: Mounted in Black Anodized Ring
Transmitted Wavefront, RMS: λ/4 (prior to coating)
Compatible Fluorophore: FITC Emission
Environmental Durability: Humidity per MIL-STD-810H, Section 507.6 Temperature per MIL-STD-810H, Section 501.7 and 502.7
Physical Durability: Adhesion per MIL-PRF-13830B, Section C.4.5.12 Moderate abrasion per MIL-PRF-13830B, Section C.4.5.11 Cleaning per MIL-C-48497A Section 4.5.4.2
Mount Thickness (mm): 3.5 ±0.1
Substrate Thickness (mm): 2.00 ±0.25

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant