



## 58 x 60mm Lenslet Array, 7 x 5.4mm Lenslets



Multi-Lens Arrays



Stock **#63-231** **4 In Stock**

MRP ₹13,578

! Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-10	₹13,578 each
Qty 11-25	₹10,614 each
Qty 26-49	₹10,041 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Type:  
Lens Array

### Physical & Mechanical Properties

Dimensions (mm):

58.0 x60.0

22.00 ±2%

Radius of Lenslet (mm):

3.00 ±0.2

Thickness (mm):

### Optical Properties

41.90 Effective Focal Length EFL (mm):

B270 Substrate: □

BBAR (400-700nm) Coating:

400 - 700 Wavelength Range (nm):

### Regulatory Compliance

Compliant RoHS 2015:

View Certificate of Conformance:

Japan Country of Origin:

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Integrated, Monolithic Design
- Single Sided Arrays Create Even Illumination in Pairs
- Double Sided Arrays Ideal for Laser Top Hat Profile Generation

Multi-Lens Arrays are an all glass monolithic design which yields higher transmission, superior stability, and affordability when compared to cemented or plastic varieties. These lenses are available as single-sided or double-sided arrays to meet requirements for illumination, projection, and laser systems. The single-sided arrays are used to create square spot patterns or to create even illumination when used in pairs. Decreasing the spacing between the two lens arrays will increase the illuminated area while increasing the spacing will decrease the area. Double sided lens arrays are ideal for use with laser sources to create top hat output profiles, ensuring uniform illumination for machine vision and microscopy applications.

## Technical Information

A	B	C	D	Stock No.
46.06mm	46.06mm	4mm	3mm	#63-230
58mm	60mm	7mm	5.4mm	#63-231

