

[See all 56 Products in Family](#)

**TECHSPEC® 550nm CWL, 25mm Dia., Hard Coated OD 4.0 50nm Unmounted Bandpass Filter**



TECHSPEC® Unmounted OD 4.0 Bandpass Filters

Stock #15-166 **14 In Stock**

[Additional Bandwidths](#)

1 MRP ₹28,249

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹28,249 each
Qty 6-25	₹22,599 each
Qty 26-49	₹21,187 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Bandpass Filter

Type:

Typical Applications:  
Acridine Yellow, Magnesium Orange, HiLyte Fluor 555

**Physical & Mechanical Properties**

25.00 ±0.10	<b>Diameter (mm):</b>
22.5	<b>Clear Aperture CA (mm):</b>
3.30 ±0.20	<b>Thickness (mm):</b>
Unmounted	<b>Construction:</b>
<b>Physical Durability:</b> Adhesion per ML-PRF-13830B, Section C.4.5.12 Moderate abrasion per ML-PRF-13830B, Section C.4.5.11 Cleaning per ML-C-48497A Section 4.5.4.2	
Protective as needed	<b>Bevel:</b>

## Optical Properties

0	<b>Angle of Incidence (°):</b>
≥4.0	<b>Optical Density OD (Average):</b>
550.00 ±5	<b>Center Wavelength CWL (nm):</b>
50.00 ±5	<b>Full Width-Half Max FWHM (nm):</b>
Optical Glass	<b>Substrate:</b> <input type="checkbox"/>
≥90 (Average over bandwidth)	<b>Minimum Transmission (%):</b>
Hard Coated	<b>Coating:</b>
80-50	<b>Surface Quality:</b>
200 - 1200	<b>Blocking Wavelength Range (nm):</b>

## Environmental & Durability Factors

<b>Environmental Durability:</b> Humidity per ML-STD-810H, Section 507.6 Temperature per ML-STD-810H, Section 501.7 and 502.7	
---	--

## Regulatory Compliance

Compliant	<b>RoHS 2015:</b>
View	<b>Certificate of Conformance:</b>
Compliant	<b>Reach 247:</b>
United States	<b>Country of Origin:</b>
<b>Imported By:</b> Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Center Wavelengths from 365 to 1550nm
- 10, 25, or 50nm Full-Width Half Maximum Options
- High Transmission and Deep Blocking
- Mounted OD 4.0 [5nm](#), [10nm](#), [25nm](#) and [50nm](#) Bandpass Filters Also Available

TECHSPEC® Unmounted OD 4.0 Bandpass Filters are available with a 10, 25, or 50nm full-width half maximum (FWHM). The narrowband 10nm bandpass filters are ideal for laser line separation, flame photometry, or chemical detection applications. The broadband 25 and 50nm filters are used in a variety of life science and machine vision applications, including preventing photobleaching of fluorophores and improving the signal to noise ratio of imaging

systems. TECHSPEC Unmounted OD 4.0 Bandpass Filters are designed with center wavelengths from 365 to 1550nm, covering common laser lines and spectral lines, and provide OD 4.0 blocking outside of their passband. Standard diameter sizes of 12.5 and 25mm facilitate integration into benchtop optical systems or life science instrumentation.

## Compatible Mounts

---