

TECHSPEC® 5mm, 1064nm V-Coat, Laser Line Fused Silica Right Angle Prism



Stock #83-329 5 In Stock

-

1

+

MRP ₹15,718

Price inclusive of all taxes

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | ₹15,718 each                  |
| Qty 6-25       | ₹12,532 each                  |
| Qty 26-49      | ₹11,788 each                  |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| General                          |                             |
|----------------------------------|-----------------------------|
| Right Angle Prism                | Type:                       |
| Physical & Mechanical Properties |                             |
| +0.00/-0.10                      | Dimensional Tolerance (mm): |
| Protective as needed             | Bevel:                      |

|                                           |                                                       |
|-------------------------------------------|-------------------------------------------------------|
| 7.10                                      | Length of Hypotenuse (mm):                            |
| 5.00                                      | Length of Legs (mm):                                  |
| Optical Properties                        |                                                       |
| ±40                                       | Angle Tolerance (arcsec):                             |
| Laser V-Coat (1064nm)                     | Coating:                                              |
| 1064                                      | Design Wavelength DWL (nm):                           |
| Fused Silica (Corning 7980)               | Substrate: <input type="checkbox"/>                   |
| 20-10                                     | Surface Quality:                                      |
| ±1                                        | Pyramid Tolerance (arcmin):                           |
| Left-Handed                               | Image Orientation:                                    |
| R <sub>abs</sub> <0.25% @ 1064nm          | Coating Specification:                                |
| 90                                        | Ray Deviation (°):                                    |
| 15 J/cm <sup>2</sup> @ 1064nm, 20ns, 20Hz | Damage Threshold, By Design: <input type="checkbox"/> |
| 1.25                                      | Power (fringes) @ 632.8nm:                            |
| 0.20                                      | Irregularity (fringes) @ 632.8nm:                     |

|                                                                                                                                                                                                         |                             |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------|
| Regulatory Compliance                                                                                                                                                                                   |                             |
| Compliant                                                                                                                                                                                               | RoHS 2015:                  |
| Compliant                                                                                                                                                                                               | Reach 209:                  |
| View                                                                                                                                                                                                    | Certificate of Conformance: |
| Singapore                                                                                                                                                                                               | Country of Origin:          |
| Edmund Optics India Private Limited<br>267, Greystone Building, Second Floor,<br>6th Cross Rd, Binnamangala,<br>Stage 1, Indiranagar, Bengaluru,<br>Karnataka, India 560038<br>Phone: +91- 80-6845 0000 | Imported By:                |

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume


Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details



- 355nm, 532nm and 1064nm Options Available
- High Damage Threshold
- Ray Deviation of 90°
- Additional [Right Angle Prisms](#) Available

TECHSPEC® High Power Laser Line Fused Silica Right Angle Prisms provide high damage thresholds ranging from 2 - 5J/cm<sup>2</sup> allowing for easy integration into most Nd:YAG laser systems. They feature low arcsecond angle tolerance and are made from precision UV fused silica, making them ideal for laser based applications requiring precise alignment.


Right angle prisms are generally used to bend image paths or redirect light at 90°. This produces a left handed image and depending on the orientation of the prism, the image may be inverted or reverted. Right angle prisms can also be used in combination for image/beam displacement.




Technical Information




Right Angle Prism Ray Path



Right Angle Prism Ray Path



Right Angle Prism Tunnel Diagram



Right Angle Prism Tunnel Diagram