

[See all 2 Products in Family](#)

55mm Focal Length Partially Telecentric Video Lens



55mm Focal Length Partially Telecentric Video Lens, #52-271

Stock #52-271 **16 In Stock**

MRP ₹77,905

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹77,905 each
Need More?	Request Quote

Product Downloads

General

Product Family:
55mm FL Partially-Telecentric Imaging Lenses

Note:
 PMAG: Non-Telecentric: 0.5X - 0X
 Telecentric: 0.5X - 0.4X
 Working Distance (mm): Non-Telecentric: 127 - ∞
 Telecentric: 127 - 158.75

Type:
Telecentric Lens

Special Type of Lens:

Partially Telecentric

Physical & Mechanical Properties

Variable **Iris Option:**

92.90 **Length (mm):**

53 **Maximum Diameter (mm):**

53 **Outer Diameter (mm):**

314.68 **Weight (g):**

Optical Properties

Horizontal Field of View, 1/2" Sensor:
Non-Telecentric: 12.8mm - 6.7°
Telecentric: 12.8 - 16.0mm

11.00 **Maximum Image Circle (mm):**

55.00 **Focal Length FL (mm):**

0.5X - 0.4X **Primary Magnification PMAG:**

127 - 158.75 **Working Distance (mm):**

f/2.8 - f/32 **Aperture (f#):**

<1.0 **Distortion (%):**

0.5X - 0.4X **Magnification:**

1 **Maximum Distortion (%):**

VIS **Lens Wavelength Range:**

Sensor

2/3" **Maximum Sensor Format:**

7.00 **Pixel Size (µm):**

Threading & Mounting

M43 x 0.75 **Filter Thread:**

C-Mount **Mount:**

Regulatory Compliance

[Exempt](#) **RoHS 2015:**

[Contains SVHC\(s\)](#) **Reach 224:**

[View](#) **Certificate of Conformance:**

Japan **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000



Product Details

- 2/3", C-Mount Lens
- Up to 1.3 MegaPixels, 7µm Pixel Size Sensors
- Function as Both Macro and Telecentric Lens
- ±12.5mm of Object Movement Before 1% Error Image Scale Occurs

55mm FL Partially-Telecentric Imaging Lenses allow ±12.5mm of object movement (at 0.5X magnification) before a 1% error in image scale occurs, while conventional lenses permit typically ±1.7mm of movement under the same conditions. Telecentric lenses yield constant magnification over a range of working distances, virtually eliminating viewing angle error. The lens' protective window (at C-Mount end) needs to be removed for use with adapter lenses. 55mm FL Partially-Telecentric Imaging Lenses are ideal in machine vision applications requiring accurate measurement of three-dimensional objects with slight height variations. By eliminating the perspective distortion and magnification error inherent in conventional lenses, they yield dimensionally accurate images that are easily interpreted by software.

For mounting these lenses, our [Industrial Boom Stands](#) and mounting adapters are recommended as workstation platforms. Ring light guides can not be mounted directly on this lens because of the front focusing adjustment.

Technical Information



	Telecentric Specifications		Non-Telecentric Specifications	
	Lens with 2X Converter	Lens with 2X Converter	Lens with 2X Converter	Lens with 0.75X Converter
Primary Magnification PMAG	1.0X - 0.4X (full range)	1.0X - 0X	1.0X - 0X	0.375X - 0X
Field of View	6.4 - 16.0mm	6.4mm - 3.3°	6.4mm - 3.3°	17.0 - 8.9°
Working Distance	5.25" - 11.25"	5.25" - ∞	5.25" - ∞	5" - ∞