

TECHSPEC[®] 5mm 532nm, Laser Line Non-Polarizing Cube Beamsplitter



Laser Line Non-Polarizing Cube Beamsplitters



Stock **#35-958** **5 In Stock**

-

1

+

₹21,780

ADD TO CART

Volume Pricing	
Qty 1-5	₹21,780 each
Qty 6-25	₹17,460 each
Qty 26-99	₹16,110 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Non-Polarizing Beamsplitter

Type:

Physical & Mechanical Properties	
Protective as needed	Bevel:
90	Clear Aperture (%):
Cube	Construction:
5.0 x 5.0 x 5.0 ±0.1	Dimensions (mm):
Optical Properties	
±2	Beam Deviation (arcmin):
<0.25% Reflection on Entrance and Exit Faces	Coating Specification:
532	Design Wavelength DWL (nm):
±5	Reflection/Transmission Tolerance (%):
N-BK7	Substrate: 
40-20	Surface Quality:
<45% ±5% @ DWL	Transmission (%):
<3% @ DWL	Ts-Tp :
1.50	Power (fringes) @ 632.8nm:
0.25	Irregularity (fringes) @ 632.8nm:
Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 219:
View	Certificate of Conformance:

PRODUCT DETAILS

- <3% Transmission Difference for S and P Polarization States
 - AR Coated <0.25% on Entrance and Exit Faces
 - Nd:YAG and HeNe Options
- TECHSPEC® Laser Line Non-Polarizing Cube Beamsplitters offer users the ability to split light evenly into orthogonal paths regardless of the incoming polarization state. These cubes are designed with a metallic-dielectric hybrid coating that yields less than a 3% difference in transmission for S-polarized and P-polarized light. These cubes are compatible with common Nd:YAG and HeNe lasers and are available with three beamsplitter coating options at 1064nm, 632nm, and 532nm. Efficiency is enhanced with AR coatings on the entrance and exit faces featuring <0.25% reflection per surface. TECHSPEC® Laser Line Non-Polarizing Cube Beamsplitters will displace a beam by less than 2 arcmin, making them easy to integrate into alignment sensitive applications.

LASER OPTICS

MADE BY EDMUND OPTICS®



LEARN MORE

TECHNICAL INFORMATION

