

5mm Dia., 1mm Thick, 400-1100nm HDAR Coated Fused Silica Window



Stock **#29-974** 20+ In Stock

-

1

+

₹12,836

ADD TO CART

Volume Pricing	
Qty 1-5	₹12,836 each
Qty 6-25	₹10,269 each
Qty 26-49	₹9,627 each
Need More?	Request Quote

Product Downloads

General	
Protective Window	Type:
Physical & Mechanical Properties	
Protective as needed	Bevel:
80	Clear Aperture (%):

4.00	Clear Aperture CA (mm):
5.00 +0.00/-0.10	Diameter (mm):
1.00 ±0.10	Thickness (mm):
Fine Ground	Edges:
522.00	Knoop Hardness (kg/mm²):
<5	Parallelism (arcsec):
0.16	Poisson's Ratio:
73	Young's Modulus (GPa):

Optical Properties	
67.8	Abbe Number (v _d):
Hardened VIS-NIR (400-1100nm)	Coating:
R _{avg} <1.5% @ 400 - 1100nm R _{abs} <2.0% @ 400 - 1100nm	Coating Specification:
1.458	Index of Refraction (n _d):
Fused Silica	Substrate:
20-10	Surface Quality:
λ/10	Transmitted Wavefront, P-V:
400 - 1100	Wavelength Range (nm):
-80 to +160 per MIL-M-13508C Paragraph 4.4.4	Coating Temperature (°F):

Material Properties	
0.52 (+5 to +35°C) 0.57 (0 to +200°C) 0.48 (-100 to +200°C)	Coefficient of Thermal Expansion CTE (10 ⁻⁶ /°C):
2.20	Density (g/cm³):

Environmental & Durability Factors	
Severe, per MIL-C-675C Paragraph 4.5.10	Coating Abrasion:
Per MIL-M-13508C Paragraph 4.4.6	Coating Adhesion:
≥24 Hours per MIL-C-675C paragraph 4.5.8	Coating Humidity:
≥24 Hours Immersion per MIL-C-675C paragraph 4.5.7	Coating Salt Solubility:
≥24 Hours per MIL-C-675C paragraph 4.5.9	Coating Salt Spray:

Regulatory Compliance	
View	Certificate of Conformance:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- HDAR Coating Achieves Severe Abrasion Requirements of MIL-C-675C
 - Low Reflectivity Across the VIS-NIR
 - Ideal for Use in Harsh Environments
 - [Uncoated Fused Silica Windows](#) Also Available
- High Durability Anti-Reflection (HDAR) Coated Fused Silica Windows feature precision fused silica substrates with rugged HDAR coatings where frequent handling or cleaning are required. Similar to [diamond-like carbon \(DLC\) coatings](#), the HDAR coatings are designed to withstand temperature cycling from -80 to +160°F, high humidity for 24 hours, salt spray for a continuous period of 24 hours, and salt solubility for an immersion period of 24 hours. These

coatings are deposited on fused silica which has excellent mechanical and thermal stability, ensuring high performance even in harsh environments. High Durability Anti-Reflection (AR) Coated Fused Silica Windows are ideal for aerospace, defense, and industrial applications, as well as any optical application requiring durable protective windows.
