

**TECHSPEC® 5mm Dia., 1mm Thick, NIR I Coated, λ/4 Fused Silica Window**



TECHSPEC® λ/4 UV Fused Silica Windows

Stock **#18-333** 10 TO 12 DAYS



1



**₹9,353.00**

ADD TO CART

Qty 1-5

₹9,353.00

Qty 6+

₹7,482.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



**Abbe Number (v<sub>d</sub>):**  
67.8

**Bevel:**  
Protective as needed

**Clear Aperture (%):**  
90

|                                                                                                                                                   |
|---------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Clear Aperture CA (mm):</b><br>4.50                                                                                                            |
| <b>Diameter (mm):</b><br>5.00 +0.00/-0.10                                                                                                         |
| <b>Thickness (mm):</b><br>1.00 ±0.10                                                                                                              |
| <b>Coating:</b><br>NIR I (600-1050nm)                                                                                                             |
| <b>Coating Specification:</b><br>R <sub>avg</sub> ≤0.5% @ 600 - 1050nm                                                                            |
| <b>Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):</b><br>0.52 (+5 to +35°C)<br>0.57 (0 to +200°C)<br>0.48 (-100 to +200°C)            |
| <b>Density (g/cm³):</b><br>2.20                                                                                                                   |
| <b>Edges:</b><br>Fine Ground                                                                                                                      |
| <b>Index of Refraction n<sub>d</sub>:</b><br>1.458                                                                                                |
| <b>Knoop Hardness (kg/mm²):</b><br>522                                                                                                            |
| <b>Parallelism (arcmin):</b><br><1                                                                                                                |
| <b>Poisson's Ratio:</b><br>0.16                                                                                                                   |
| <b>Substrate:</b><br><a href="#">Fused Silica</a> (Corning 7980)                                                                                  |
| <b>Surface Quality:</b><br>40-20                                                                                                                  |
| <b>Transmitted Wavefront, P-V:</b><br>λ/4                                                                                                         |
| <b>Type:</b><br>Protective Window                                                                                                                 |
| <b>Wavelength Range (nm):</b><br>600 - 1050                                                                                                       |
| <b>Young's Modulus (GPa):</b><br>73                                                                                                               |
| <b>Damage Threshold, Reference:</b> <br>7 J/cm² @ 1064nm, 10ns |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |