

TECHSPEC® 5mm Dia., 1mm Thick, VIS 0° Coated λ/4 N-BK7 Window



Stock **#23-377** [CONTACT US](#)

- 1 + **₹6,656.00**

ADD TO CART

Qty 1-5
₹6,656.00
Qty 6+
₹5,329.00
Volume Pricing
Request Quote

Get Product Downloads



Abbe Number (v_d):
64.17

Bevel:
Protective as needed

Clear Aperture (%):
90

Clear Aperture CA (mm):

4.50
Diameter (mm): 5.00 +0.00/-0.25
Thickness (mm): 1.00 ±0.20
Coating: VIS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 7.1 (-30 to +70°C) 8.3 (+20 to +300°C)
Density (g/cm³): 2.51
Edges: Fine Ground
Index of Refraction n_d: 1.516
Knoop Hardness (kg/mm²): 610
Parallelism (arcmin): <1
Poisson's Ratio: 0.206
Substrate: N-BK7
Surface Quality: 60-40
Transmitted Wavefront, P-V: λ/4
Type: Protective Window
Wavelength Range (nm): 425 - 675
Young's Modulus (GPa): 82
Damage Threshold, Reference: ☐ 5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant