

TECHSPEC® 5mm Dia. x 15mm FL, NIR II, Inked, Double-Convex Lens



Stock #67-598-INK 17 TO 22 D=DAYS

Other Coating Options

- 1 +

₹5,177.00

ADD TO CART

Qty 1-9
₹5,177.00
Qty 10+
₹4,655.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
5.00 ±0.025

Back Focal Length BFL (mm):
14.33

Effective Focal Length EFL (mm): 15.00
Coating: NIR II (750-1550nm)
Coating Specification: R _{abs} ≤1.5% @ 750 - 800nm R _{abs} ≤1.0% @ 800 - 1550nm R _{avg} ≤0.7% @ 750 - 1550nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Center Thickness CT (mm): 2.00
Center Thickness Tolerance (mm): ±0.05
Edge Thickness ET (mm): 1.58
Radius R₁=R₂ (mm): 15.16
Clear Aperture CA (mm): 4.50
f#: 3.00
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1.00
Numerical Aperture NA: 0.17
Type: Double-Convex Lens
Wavelength Range (nm): 750 - 1550
Damage Threshold, By Design: ☐ 8 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View