

TECHSPEC[®] 5mm Dia. x 12.5mm FL, VIS-NIR Coated, Achromatic Lens



Stock **#49-947** 10 TO 12 DAYS
[Other Coating Options](#)

-

1

+

₹7,569.00

ADD TO CART

Qty 1-5
₹7,569.00
Qty 6+
₹6,047.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
5.00 +0.0/-0.025

Effective Focal Length EFL (mm):
12.50

Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 10.89
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 4.5
Centering (arcmin): <1
Center Thickness CT (mm): 3.30 ±0.10
Center Thickness CT 1 (mm): 2.30 ±0.05
Center Thickness CT 2 (mm): 1.00 ±0.05
Radius R₁ (mm): 8.57
Radius R₂ (mm): -6.22
Radius R₃ (mm): -21.36
Edge Thickness ET (mm): 2.78
Substrate: ☐ N-SSK6 / N-SF56
Surface Quality: 40-20
f/#: 2.5
Numerical Aperture NA: 0.20
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 400 - 1000

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View