

5mm FL Wide Angle Low Distortion Lens



#68-670

Stock **#68-670** 20+ In Stock

1 MRP ₹93,228

Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1+	₹93,228 each
Need More?	Request Quote

Product Downloads

General

Product Family:
Low Distortion Wide Angle Lenses

Type:
Fixed Focal Length Lens

Physical & Mechanical Properties

Iris Option:
Fixed

Length (mm):
38.20

42.0	Maximum Diameter (mm):
42	Outer Diameter (mm):
75.00	Weight (g):

Optical Properties

200.00	Field of View @ Min Working Distance (mm):
82.4°	Horizontal Field of View, 2/3" Sensor:
65.2°	Horizontal Field of View, 1/2" Sensor:
11.00	Maximum Image Circle (mm):
5.00	Focal Length FL (mm):
150 - ∞	Working Distance (mm):
f/2.8	Aperture (f/#):
<0.5	Distortion (%):
<0.5	Maximum Distortion (%):
VS	Lens Wavelength Range:

Sensor

2/3"	Maximum Sensor Format:
4.50	Pixel Size (µm):

Threading & Mounting

M40.5 x 0.50	Filter Thread:
C-Mount	Mount:

Regulatory Compliance

View	Certificate of Conformance:
Japan	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details

- Up to 1/2.5", C-Mount and CS-Mount options
- Up to 3 MegaPixel and Down to 1% Distortion
- No Refocusing from 100mm to Infinity
- 1.28mm to 40mm Focal Length

Low Distortion Wide Angle Lenses maintain high resolution for applications with long working distance requirements and can accommodate multi-megapixel camera sensors. The optical design of these low-distortion wide-angle lenses enables users to achieve less than 3% distortion over a 125° field of view, or less than 1% distortion over a 110° field of view. These lenses feature a locking screw for the manual iris enabling the use in high vibration environments. Low Distortion Wide Angle Lenses are ideal for security and surveillance, machine vision, or [factory automation](#) applications. These lenses do not require refocusing from 100mm to Infinity.

Note: Image will be flipped (180° rotation). Auto Iris Options require cameras with P-Iris or DC Iris control.