

[See all 12 Products in Family](#)

TECHSPEC® 5mm Uncoated, High Tolerance Fused Silica Right Angle Prism



TECHSPEC High Tolerance UV Fused Silica Right Angle Prisms

Stock **#47-200** **12 In Stock**

1 MRP ₹9,989

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹9,989 each
Qty 6-25	₹7,996 each
Qty 26-49	₹7,492 each
Need More?	Request Quote

Product Downloads

General

Right Angle Prism **Type:**

Physical & Mechanical Properties

+0.0/-0.1 **Dimensional Tolerance (mm):**

Bevel:

Protective as needed

7.10 Length of Hypotenuse (mm):

5.00 Length of Legs (mm):

Optical Properties

±40 Angle Tolerance (arcsec):

Uncoated Coating:

Fused Silica (Corning 7980) Substrate:

20-10 Surface Quality:

±1 Pyramid Tolerance (arcmin):

Left-Handed Image Orientation:

200 - 2200 Wavelength Range (nm):

1.25 Power (fringes) @ 632.8nm:

0.20 Irregularity (fringes) @ 632.8nm:

Regulatory Compliance

Compliant RoHS 2015:

Compliant Reach 219:

View Certificate of Conformance:

Singapore Country of Origin:

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Ray Deviation of 90°
- Left Handed Image
- ±40 Arcseconds Angle Tolerance
- Additional [Right Angle Prism](#) Options Available

TECHSPEC® High Tolerance Fused Silica Right Angle Prisms, like most right angle prisms, are used to bend image paths or redirect light at 90°. This produces a left-handed image and depending on the orientation of the prism, the image may be inverted or reverted. Right angle prisms can also be used in combination for image/beam displacement. TECHSPEC® High Tolerance Fused Silica Right Angle Prisms feature low arcsecond angle tolerance and are made from precision UV fused silica for use in a variety of UV, Visible and NIR applications. The prisms are offered in leg lengths from 5 to 25mm.

Technical Information



UV FS Transmission Curve