

[See all 7 Products in Family](#)

3W Deuterium/3W Tungsten Lamp Source (UV-VIS-NIR Range)



3W Deuterium/3W Tungsten Lamp Source (UV-VIS-NIR Range), #57-055

Stock **#57-055** **1 In Stock**

MRP ₹3,18,069

Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1+	₹3,18,069 each
Need More?	Request Quote

Product Downloads

General

Note:
External power supply and AC cord included. Fiber patchcord listed under Accessories tab sold separately.

Lamp Lifetime (hours):
≥1000 / ≥2000

Physical & Mechanical Properties

Dimensions (mm):
171 x 76 x 64

Optical Properties

Wavelength Range (nm):
200 - 1100

Electrical

Output Power (W):
3W Deuterium, 3W Tungsten, 6W Both

Hardware & Interface Connectivity

Connector:
SMA-905

Regulatory Compliance

Certificate of Conformance:
[View](#)

Country of Origin:
United States

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Designed for Use with [Spectrometers](#)
- Lamps Available for UV to NIR
- Xenon, Tungsten, or Deuterium Sources

Broadband Fiber-Coupled Light Sources are ideal for use in a variety of spectroscopy applications and for coupling with the Fiber Optic Reflectance Sphere. The pulsed Xenon source is designed for applications from the UV to visible. The Tungsten source is designed for applications in the visible to NIR. The Deuterium/Tungsten source is ideal for applications requiring wide spectral ranges from the UV to NIR.