

TECHSPEC[®] 600-1000nm, 50mm Diameter Ultrafast-Enhanced Silver Coated, λ /10 Mirror



Stock #21-991 8 In Stock

-

1

+

MRP ₹23,608

 Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹23,608 each
Qty 6-25	₹18,867 each
Qty 26-49	₹17,656 each
Need More?	Request Quote

Product Downloads

General	
Flat Mirror	Type:
Physical & Mechanical Properties	
50.00 +0.00/-0.20	Diameter (mm):
5.00 ±0.20	Thickness (mm):

	Back Surface:
Commercial Polish	
	Bevel:
Protective as needed	
	Clear Aperture (%):
90	
	Dimensional Tolerance (mm):
+0.00/-0.20	
	Edges:
Ground	
	Parallelism (arcsec):
30	

Optical Properties	
	Wavelength Range (µm):
0.60 - 1.05	
	Coating Type:
Metal	
	Coating:
Ultrafast-Enhanced Silver (600-1000nm)	
	Surface Flatness (P-V):
λ/10	
	Wavelength Range (nm):
600 - 1000	
	Substrate: ☐
Fused Silica (Corning 7980)	
	Coating Specification:
R _{avg} >99% @ 600 - 1000nm, 0° R _s >99% @ 540 - 1000nm, 45° R _p >98.5% @ ~730 - 870nm, 45°	
	Surface Quality:
20-10	
	Damage Threshold, Reference: ☐
0.3 J/cm² @ 800nm, 48fs, 1 pulse (typical) 0.16 J/cm² @ 800nm, 48fs, 100Hz, 1000 pulses (typical)	
	GDD Specification:
0 ±20fs² @ 600 - 1000nm	

Regulatory Compliance	
	Certificate of Conformance:
View	
	Country of Origin:
United States	
	Imported By:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Precision Fused Silica Substrate
- Variety of Sizes and Coating Options Available
- Low Coefficient of Thermal Expansion

TECHSPEC® λ/10 First Surface Mirrors are ideal for demanding beam steering and reflection applications in the visible and IR spectra. With a precision fused silica substrate, the mirrors feature a low coefficient of thermal expansion while being highly durable and resistant to abrasion. These precision mirrors are available in a variety of sizes and coating options, including enhanced aluminum, protected gold, and protected silver. These coatings allow for improved handling of the component, increased durability of the metal coating, and protection from oxidation with little impact to the performance on the metal coating. TECHSPEC® λ/10 First Surface Mirrors can be utilized in various optics and photonics applications, including biotech instruments such as DNA sequencers and polymerase chain reaction (PCR) testing platforms.

Note: Surface flatness is measured before coating.

Technical Information



600-1000nm Ultrafast-Enhanced Silver

Compatible Mounts

;