


TECHSPEC®

600 x 450mm Linear Polarizing Film (XP42-40)



Stock #14-343

CLEARANCE

CONTACT US

-

1

+

₹22,620.00

ADD TO CART

Qty 1-10
₹22,620.00
Qty 11+
₹20,010.00
Volume Pricing
Request Quote

Get Product Downloads

Extinction Ratio:

9000:1 (nominal at 555nm)

Substrate:

[Polymer Film XP42-40](#)

Operating Temperature (°C):

-40 to +80

Dimensions (mm):

600.0 x 450.0

Thickness (mm): 0.40 ±0.05
Transmission (%): Single: 42 ±2 Parallel: 36.4 Crossed: <0.004 (nominal at 555nm)
Type: Linear Polarizer
Dimensional Tolerance (mm): +0.0/-3.0
Construction: Polarizing Film
Note: Polarization axis can be identified as follows: Circular Parts - Parallel to direction of notch on polarizer Square Parts - Parallel to mark on protective film Rectangular Parts - Parallel to first listed dimension
Wavelength Range (nm): 400 - 700
Polarization Efficiency (%): >99.98 (nominal at 555nm)
#Sorting: 53.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Contains SVHC(s)