

TECHSPEC® 600 x 450mm Linear Polarizing Film (XP42-40)



Stock #29-498 9 In Stock

-

1

+

₹20,630

ADD TO CART

Volume Pricing	
Qty 1-10	₹20,630 each
Qty 11+	₹18,217 each
Need More?	Request Quote

Product Downloads

General

Type:

Linear Polarizer

Note:

Polarization axis is parallel to marking on protective film.

Physical & Mechanical Properties

Dimensions (mm):

600.0 x 450.0 ±5.0

Thickness (mm):

0.40 ±0.05	
Construction:	
Polarizing Film	
Optical Properties	
Coating:	
Uncoated, Protective Film on Both Sides	
Extinction Ratio:	
9000:1 (nominal at 555nm)	
Substrate: ☐	
Polymer Film XP42-40	
Transmission (%):	
Single: 42 ±2 Parallel: 36.4 Crossed: <0.004 (nominal at 555nm)	
Wavelength Range (nm):	
400 - 700	
Polarization Efficiency (%):	
>99.98 (nominal at 555nm)	
Transmission, Single (%):	
42 ±2	
Transmission, Parallel (%):	
36.4	
Transmission, Crossed (%):	
<0.004 (nominal at 555nm)	
Regulatory Compliance	
RoHS 2015:	
Compliant	
Certificate of Conformance:	
View	
Reach 235:	
Compliant	
Country of Origin:	
Japan	
Imported By:	
Edmund Optics India Private Limited	

Product Details

- High Transmission of Unpolarized Light from 400 – 700nm
- Excellent Extinction Ratio of 9000:1
- Available in Custom Sizes
- [High-Temperature](#) Options Also Available



Ideal for a range of imaging applications, TECHSPEC® High Contrast Linear Polarizing Film (XP42) features an excellent extinction ratio and high transmission from 400 – 700nm. This polarizing film is offered in multiple thicknesses; thicker polarizing film has increased rigidity. Available in sheets, TECHSPEC® High Contrast Linear Polarizing Film (XP42) can be cut to fit any application need.

Note: Polarizer Film with adhesive available.

Immediate Custom Quotes Available

If you have a need for any round, square, or rectangular size of a TECHSPEC High Contrast Linear Polarizing Film (XP42) in dimensions between 3mm and 600mm, please visit our [Polarizing Film Tool](#). We'll provide an immediate quote, and can deliver the part to your requested size in approximately 3 weeks. A full list of standard manufacturing tolerances and restrictions are listed. For fully customized polymer polarizers to your requirements, visit our [Customized Polymer Polarizers Capabilities](#) page.

Technical Information





;