

TECHSPEC® 600 x 900mm Linear Plastic Polarizer (XP42-300)



Stock #24-284 3 In Stock

-

1

+

₹49,147

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹49,147 each
Qty 6-49	₹39,318 each
Qty 50-99	₹36,883 each
Need More?	Request Quote

Product Downloads

General	
Linear Polarizer	Type:
Physical & Mechanical Properties	
600.0 x 900.0 ±5.0	Dimensions (mm):
3.21 ±0.35	Thickness (mm):

Polarizing Film on PMMA		Construction:
Optical Properties		
9000:1		Extinction Ratio:
XP42-300 on PMMA		Substrate: □
Single: 42 Parallel: 36 Crossed: <0.004		Transmission (%):
400 - 700		Wavelength Range (nm):
>99.98		Polarization Efficiency (%):
Environmental & Durability Factors		
-40 to +80		Operating Temperature (°C):
Regulatory Compliance		
Compliant		RoHS 2015:
View		Certificate of Conformance:
Compliant		Reach 235:
Japan		Country of Origin:
Edmund Optics India Private Limited		Imported By:

Product Details

- Excellent Extinction Ratio of 9000:1
- Increased Durability through Lamination on PMMA
- High Transmission of Unpolarized Light from 400 – 700nm

TECHSPEC® High Contrast Plastic Linear Polarizers (XP42-200 & XP42-300) are ideal for a variety of imaging applications. Offered in multiple sizes, these linear polarizers feature an excellent extinction ratio and high transmission of unpolarized light from 400 – 700nm. The plastic substrate results in a lightweight polarizer, ideal for weight constrained applications. TECHSPEC® High Contrast Plastic Linear Polarizers (XP42-200 & XP42-300) offer increased durability compared to [polarizing film](#).

When unpolarized light enters a linear polarizer, the light that is polarized perpendicular to the polarization axis is absorbed, and light parallel to the polarization axis is transmitted. TECHSPEC® High Contrast Plastic Linear Polarizers (XP42-200) utilize a stretched PVA film to create the polarization axis. To increase durability, the film is then laminated between two plastic plates.

Note: These linear polarizers are not recommended for laser applications.

Immediate Custom Quotes Available

If you have a need for any round, square, or rectangular size of a TECHSPEC High Contrast Plastic Linear Polarizers (XP42-200) in dimensions between 3mm and 600mm, please visit our [Polarizing Film Tool](#). We'll provide an immediate quote, and can deliver the part to your requested size in approximately 3 weeks. A full list of standard manufacturing tolerances and restrictions are listed. For fully customized polymer polarizers to your requirements, visit our [Customized Polymer Polarizers Capabilities](#) page.

Technical Information

