


TECHSPEC[®] 600nm, 25mm Diameter, Dichroic Shortpass Filter



TECHSPEC Dichroic Shortpass Filters

Stock #69-204 10 In Stock

-

1

+

₹13,546

ADD TO CART

Volume Pricing	
Qty 1-5	₹13,546 each
Qty 6-25	₹10,588 each
Qty 26-49	₹9,809 each
Need More?	Request Quote

Product Downloads

General

Dichroic Filter

Type:

Physical & Mechanical Properties

25.00

Diameter (mm):

1.05 ±0.1

Thickness (mm):

+0.0/-0.2	Dimensional Tolerance (mm):
Adhesion per ML-PRF-13830B, Section C.4.5.12 Moderate abrasion per ML-PRF-13830B, Section C.4.5.11 Cleaning per ML-C-48497A Section 4.5.4.2	Physical Durability:
Optical Properties	
45	Angle of Incidence (°):
600.00	Cut-Off Wavelength (nm):
Fused Silica (Corning 7980)	Substrate: ☐
Hard Coated	Coating:
>80	P-Polarization Transmission (%):
>97 Average Polarization	Reflection (%):
625 - 795	Reflection Wavelength (nm):
>80	S-Polarization Transmission (%):
60-40	Surface Quality:
>85 Average Polarization	Transmission (%):
400 - 580	Transmission Wavelength (nm):
λ/4	Transmitted Wavefront, RMS:
3.00	Slope Factor (%):
±2	Cut-Off Tolerance (%):
>95	S-Polarization Reflection (%):
>95	P-Polarization Reflection (%):
Surface 1: Hard Dielectric Sputtered Surface 2: AR Coated	Coating Specification:
400 - 795	Wavelength Range (nm):
Environmental & Durability Factors	
Humidity per ML-STD-810H, Section 507.6 Temperature per ML-STD-810H, Section 501.7 and 502.7	Environmental Durability:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).


Product Details

- Sharp Cut-Off Wavelength
- Broad Transmission and Reflection Ranges
- Available in a Range of Common Sizes

Our TECHSPEC® Dichroic Shortpass Filters are designed for a 45° angle of incidence. The rejected light is reflected at 90°, making these filters ideal for use in fluorescence applications or as spectral beamsplitters. The filters feature low polarization dependence, broad spectral ranges, and a precision fused silica substrate. TECHSPEC® Dichroic Shortpass Filters have a sharp cut-off wavelength and are available in a wide range of sizes for ease of system integration. These filters can be combined with TECHSPEC® Dichroic Longpass Filters to create custom bandpass filters.

Note: The chevron on the edge of the filter points towards surface S1 with the primary filter coating on which the light should be incident.

Technical Information



Compatible Mounts