


[See all 14 Products in Family](#)

# 60mm Center of Rotation, High Vacuum (10<sup>-6</sup> Torr) Motorized Goniometer Stage, Integrated Controller

See More by [Zaber™](#)



Stock **#74-721** NEW **1 In Stock**

-

1

+

₹5,45,229

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | ₹5,45,229 each                |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| General                         |  |
|---------------------------------|--|
| Type:                           |  |
| Metric                          |  |
| Encoder:                        |  |
| No                              |  |
| Manual Control/ LED Indicators: |  |
| No                              |  |
| Manufacturer:                   |  |
| Zaber Technologies Inc.         |  |

|                                                                                     |                                 |
|-------------------------------------------------------------------------------------|---------------------------------|
| X-GSM60-SV2T9                                                                       | Model Number:                   |
| Requires Accessory Kit, <a href="#">#75-301</a> , for operation.                    | Note:                           |
| 2-Phase Stepper                                                                     | Type of Motor:                  |
| Physical & Mechanical Properties                                                    |                                 |
| Goniometer                                                                          | Type of Movement:               |
| Crossed Roller Bearing                                                              | Guide System:                   |
| 72.7 x 116.3                                                                        | Stage Size (mm):                |
| ±7                                                                                  | Travel (°):                     |
| 0.06                                                                                | Accuracy (°):                   |
| <0.01                                                                               | Backlash (°):                   |
| 20.8                                                                                | Height (mm):                    |
| 3                                                                                   | Load Capacity (kg):             |
| 30                                                                                  | Load Capacity (N):              |
| 60                                                                                  | Radius R (mm):                  |
| <0.005                                                                              | Repeatability (°):              |
| <0.087                                                                              | Resolution (μrad):              |
| 0.000069 - 30                                                                       | Speed (°/s):                    |
| 0.32                                                                                | Weight (kg):                    |
| Electrical                                                                          |                                 |
| 350                                                                                 | Current (mA):                   |
| 350                                                                                 | Maximum Operating Current (mA): |
| Hardware & Interface Connectivity                                                   |                                 |
| Precision Worm Gear                                                                 | Type of Drive:                  |
| 24-48 VDC; Power Supply w/US Plug found in accessories kit, <a href="#">#75-301</a> | Power Supply:                   |
| RS-232, USB                                                                         | Computer Interface:             |
| Material Properties                                                                 |                                 |
| High vacuum (10 <sup>-6</sup> Torr)                                                 | Vacuum Compatibility:           |
| Environmental & Durability Factors                                                  |                                 |
| 0 to +50                                                                            | Operating Temperature (°C):     |
| Regulatory Compliance                                                               |                                 |
| <a href="#">Compliant</a>                                                           | RoHS 2015:                      |
| <a href="#">View</a>                                                                | Certificate of Conformance:     |
| <a href="#">Compliant</a>                                                           | Reach 247:                      |
| Canada                                                                              | Country of Origin:              |
| Edmund Optics India Private Limited                                                 | Imported By:                    |

## Product Details

- Low Vacuum ( $10^{-3}$  Torr) and High Vacuum ( $10^{-6}$  Torr) Options Available
- 360° Rotational, Linear, or Vertical Travel Stages, and Goniometer Options Available
- Controlled via Minimal Feed-Through Wires

Zaber™ Vacuum Compatible Motorized Stages are designed for integration into vacuum systems and are available in high vacuum  $10^{-6}$  Torr stages or low vacuum  $10^{-3}$  Torr configurations (upon request). The stage body components are specifically engineered to limit outgassing of contaminants in the vacuum chamber, the included stepper motors are designed for thermal management in high vacuum environments, and the stages can be connected to a computer interface with minimal feed-through wires. Zaber™ Vacuum Compatible Motorized Stages are available in linear, 360° rotational, and goniometric configurations, allowing for a complete 6 Degree-of-Freedom system to be constructed in a vacuum. These stages are ideal for applications operating in high vacuum conditions, such as semiconductor manufacturing and processing, or optical coating processes.

**Note:** An accessories kit, [#75-301](#), is required and sold separately.

---