

[See all 12 Products in Family](#)

## 60mm Center of Rotation, Motorized Goniometer Stage, Integrated Controller

See More by [Zaber™](#)



Stock #26-076 **1 In Stock**

1  MRP ₹2,75,935

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1+	₹2,75,935 each
Need More?	<a href="#">Request Quote</a>

**Note:** This item requires accessories for use | [Learn More](#)

### Product Downloads

### General

Metric **Type:**

No **Encoder:**

Yes **Manual Control:**

**Note:**  
Requires a 24-48 VDC power supply and either

#15-295 for USB connectivity or #15-297 for RS-232 connectivity. A data cable (#15-296 or #15-299) can be used to daisy chain multiple stages together to control simultaneously.

2-Phase Stepper **Type of Motor:**

## Physical & Mechanical Properties

Goniometer **Type of Movement:**

Crossed Roller Bearing **Guide System:**

40 x 40 **Stage Size (mm):**

±7 **Travel (°):**

0.06, Unidirectional **Accuracy (°):**

< 0.01 **Backlash (°):**

20.8 **Height (mm):**

3 **Load Capacity (kg):**

30 (Centered Load) **Load Capacity (N):**

60 **Radius R (mm):**

< 0.005 **Repeatability (°):**

1.975 **Resolution (µrad):**

Max 30 **Speed (°/s):**

0.271 **Weight (kg):**

## Electrical

350 **Current (mA):**

## Hardware & Interface Connectivity

Precision Worm Gear **Type of Drive:**

Power Supply Required and Sold Separately.  
USA: #15-294  
Europe: #15-294  
Japan: #23-662  
Korea: #33-773  
China: #15-294

USB with #15-295 RS-232 with #15-297 **Computer Interface:**

## Environmental & Durability Factors

0 to +50 **Operating Temperature (°C):**

## Regulatory Compliance

**Compliant** **RoHS 2015:**

**View** **Certificate of Conformance:**

**Compliant** **Reach 247:**

Canada **Country of Origin:**

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000 **Imported By:**

## Product Details

- 40mm and 60mm Center of Rotation Options
- Vacuum-Compatible Options
- Small Footprint with a Low Profile for Compact Systems
- 30N (~3kg) Centered Load Capacity
- Available with Integrated, 200 Counts per Revolution (CPR) Motor Mounted Encoder

Zaber™ Motorized Goniometers provide electronically controlled, precise angular adjustment of an object about a fixed point located above the center of the mounting surface. Featuring a built-in controller, these goniometers can be controlled manually with an indexed control knob or computer controlled via RS-232 communication or via USB with the included software. Encoder version are available for all travel options, with 200 Counts per Revolution (CPR) rotary quadrature encoders integrated into the stepper motor. Zaber™ Motorized Goniometers are ideal for providing tip and tilt adjustment for optical components in laser alignment and beam steering applications. These goniometers feature an interlocking alignment system to ensure a common center of rotation when the 40mm and 60mm options are stacked, and can be daisy-chained with additional stages using only one power supply for ease of system integration.

**Note:** A24-48 VDC universal power supply, data cables for daisy chaining, and computer interface cables (USB or RS-232) are sold separately as accessories.