

[See all 102 Products in Family](#)

TECHSPEC<sup>®</sup> 6.0mm Diameter x 6.0mm FL, 532nm V-Coat, PCX Lens



633nm Laser Line Coated Plano-Convex(PCX) Lenses



Stock **#65-469** 20+ In Stock

☐ Other Coating Options

-

1

+

₹3,659

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-9        | ₹3,659 each                   |
| Qty 10-25      | ₹3,309 each                   |
| Qty 26-49      | ₹2,919 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

Type:

Plano-Convex Lens

Physical & Mechanical Properties

Diameter (mm):

|                      |                           |
|----------------------|---------------------------|
| 6.00 +0.0/-0.025     |                           |
|                      | Centering (arcmin):       |
| <3                   |                           |
|                      | Center Thickness CT (mm): |
| 2.50 ±0.05           |                           |
|                      | Edge Thickness ET (mm):   |
| 1.42                 |                           |
|                      | Clear Aperture CA (mm):   |
| 5.4                  |                           |
|                      | Bevel:                    |
| Protective as needed |                           |

| Optical Properties                |                                  |
|-----------------------------------|----------------------------------|
|                                   | Effective Focal Length EFL (mm): |
| 6.00 @ 587.6nm                    |                                  |
|                                   | Back Focal Length BFL (mm):      |
| 4.60                              |                                  |
|                                   | Coating:                         |
| Laser V-Coat (532nm)              |                                  |
|                                   | Coating Specification:           |
| R <sub>abs</sub> <0.25% @ 532nm   |                                  |
|                                   | Substrate: □                     |
| N-SF11                            |                                  |
|                                   | Surface Quality:                 |
| 40-20                             |                                  |
|                                   | Power (P-V) @ 632.8nm:           |
| 1.5λ                              |                                  |
|                                   | Irregularity (P-V) @ 632.8nm:    |
| λ/4                               |                                  |
|                                   | Focal Length Tolerance (%):      |
| ±1                                |                                  |
|                                   | Radius R <sub>1</sub> (mm):      |
| 4.71                              |                                  |
|                                   | f##:                             |
| 1.00                              |                                  |
|                                   | Numerical Aperture NA:           |
| 0.50                              |                                  |
|                                   | Design Wavelength DWL (nm):      |
| 532                               |                                  |
|                                   | Damage Threshold, By Design: □   |
| 5 J/cm <sup>2</sup> @ 532nm, 10ns |                                  |


| Regulatory Compliance               |                             |
|-------------------------------------|-----------------------------|
|                                     | RoHS 2015:                  |
| Compliant                           |                             |
|                                     | Certificate of Conformance: |
| View                                |                             |
|                                     | Reach 235:                  |
| Compliant                           |                             |
|                                     | Country of Origin:          |
| Japan                               |                             |
|                                     | Imported By:                |
| Edmund Optics India Private Limited |                             |

## Product Details

- <0.25% Reflection at 532nm for 2nd Harmonic Nd:YAG Applications
  - BBAR Coating Options Also Available: [uncoated](#), [MgF<sub>2</sub>](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), [NIR II](#)
  - [405nm](#), 532nm, [633nm](#), [785nm](#), [980nm](#), [1064nm](#), and [1550nm](#) V-Coated Options Offered
- TECHSPEC® 532nm Laser Line Coated Plano-Convex (PCX) Lenses are designed for maximum throughput at the specified laser wavelength. These lenses are ideal for collecting and focusing light from laser sources and their corresponding harmonics. With a maximum reflection of <0.25% per surface at the design wavelength, the lenses will provide superior transmission in applications utilizing multiple optical components. TECHSPEC® 532nm Laser Line Coated Plano-Convex (PCX) Lenses are available Laser V-Coated in a range of other wavelengths: [405nm](#) , [633nm](#), [785nm](#), [980nm](#), [1064nm](#), and [1550nm](#). Other coating options are available, including [uncoated](#), [MgF<sub>2</sub>](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), and [NIR II](#).



## Technical Information



## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
  - High-precision surface quality and flatness
  - Tight tolerances and complex geometries
  - Scalable production—from prototype to volume
- Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Compatible Mounts