

60mm, Metric Rotary Stage



60mm Dia. Metric Rotary Stage, #55-030

Stock **#55-030** **20+ In Stock**

⊖ 1 ⊕ MRP ₹29,360

● Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1-4	₹29,360 each
Qty 5+	₹25,899 each
Need More?	Request Quote

Product Downloads

General

Metric **Type:**

Physical & Mechanical Properties

Rotary **Type of Movement:**

Slide-Fit **Guide System:**

60 Dia.	Stage Size (mm):
360 (Coarse)	Travel (°):
M16 x 1	Center Hole:
20	Concentricity (µm):
Aluminium Stage	Construction:
1°	Increments:
5	Load Capacity (kg):
None	Travel Per Knob Rotation (arcmin):
0.18	Weight (kg):

Hardware & Interface Connectivity

Manual	Type of Drive:
--------	-----------------------

Threading & Mounting

(1) M16 x 1, (3) M4 x 0.7, (4) M3 x 0.5, (4) M2 x 0.4	Mounting Threads:
---	--------------------------

Regulatory Compliance

Exempt	RoHS 2015:
------------------------	-------------------

View	Certificate of Conformance:
----------------------	------------------------------------

Contains SVHC(s)	Reach 247:
----------------------------------	-------------------

Japan	Country of Origin:
-------	---------------------------

Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:
---	---------------------

Product Details

- Precision Micrometer Drive and Manual Drive Options
 - 360° Coarse Rotation
 - Micrometer Drive Models Provide ±5° Fine Rotation
 - Black Anodized Aluminum Construction
- Metric Rotary Stages feature slide-fit guide system, enabling 360° course rotation. Micrometer drive models feature a precision metric micrometer and a switchable clamp mechanism to change between course and fine movements for precise ±5° angular adjustment at any position. The manual drive model provides a smooth manual adjustment with 360° coarse movement, 1° increments. Metric Rotary Stages feature a locking mechanism to fix the stage position. For breadboard mounting, use the [Metric Base Plates](#).

Technical Information

